




Philips O'Neill
THE STRETCH headband
headphones

40mm drivers/closed-back
Over-ear



SHO9560

The Stretch

Flexible and tough

The auto-fitting Stretch sets a new standard for durable high-def sound on the go. These robust bad boys are both super-flexible and super tough, while deluxe cushioning ensures 5-star comfort.

Powerful sound

- Dynamic 40mm drivers deliver deep, dynamic bass

Enhanced durability

- Super stretch headband for enhanced durability
- Cable stress relief to prevent breakage
- Tough tangle-free cable and reinforced connectors

Supreme comfort


- Sound isolating super soft ear cushions
- Auto fit cushioned headband

PHILIPS

O'NEILL


Highlights

High grade materials




The headband is constructed with a high grade nylon TR55 superstretch polymer ensuring these headphones are extremely tough and flexible.

Smart reinforcement



Thanks to the tough tangle-free fabric cable and reinforced connectors these headphones are built to stand up to the wear and tear of your active lifestyle.

Cable stress relief



Inspired by the latest in ski technology the cable quickly disconnects from the headband whenever the cable is caught. Simply reconnect the cable to the cable stress relief of the headphone and you can continue enjoying your music.

Auto-fit

Thanks to the clever construction and stretchable inner band The Stretch self adjusts to fit every head perfectly each time.

Comfortable for long wear



The deluxe super soft ear cushions enable you to wear your headphones for as long as you like without discomfort.

Powerful sound

With dynamic 40mm drivers these headphones deliver a crystal clear sound experience coupled with a bass thumping performance.

Specifications

Sound

- Acoustic system: Closed
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 12 - 24 000 Hz
- Impedance: 32 ohm
- Maximum power input: 50 mW
- Sensitivity: 104 dB
- Speaker diameter: 40 mm
- Type: Dynamic

Connectivity

- Cable Connection: single-sided cable
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC

Packaging dimensions

- Number of products included: 1
- Packaging type: Carton
- Packaging dimensions (W x H x D): 19.5 x 21.5 x 9 cm
- Packaging dimensions (W x H x D): 7.7 x 8.5 x 3.5 inch
- Gross weight: 0.5 kg
- Gross weight: 1.102 lb
- Nett weight: 0.353 lb
- Nett weight: 0.1601 kg
- Tare weight: 0.3399 kg
- Tare weight: 0.749 lb
- UPC: 6 09585 18879 2
- Type of shelf placement: Both

Outer Carton

- Gross weight: 1.78 kg
- Gross weight: 3.924 lb
- GTIN: 1 06 09585 18879 9
- Outer carton (L x W x H): 29.5 x 24.2 x 21.4 cm
- Outer carton (L x W x H): 11.6 x 9.5 x 8.4 inch
- Nett weight: 0.4803 kg
- Nett weight: 1.059 lb
- Number of consumer packagings: 3
- Tare weight: 1.2997 kg
- Tare weight: 2.865 lb

Product dimensions

- Product dimensions (W x H x D): 17 x 19.5 x 7.5 cm
- Product dimensions (W x H x D): 6.7 x 7.7 x 3.0 inch
- Weight: 0.16 kg
- Weight: 0.353 lb

