



Tuned for deep bass

Built to Stretch

Soft isolating cushions seal in your music so you can experience the highs and lows of the ultimate listening Journey. The flexible TR90 headband is built to brave conditions that other headphones would shy away from.

Mind-blowing sound

- Dynamic 40mm neodymium drivers deliver deep, dynamic bass
- Be immersed in beats with over-ear isolating cushions
- Jump from music to calls using built-in mic & remote control

Prepare for impact


- L-shaped connector enhances cable durability and lifespan
- Super stretchy and tough TR55 headband
- Cable quick release to prevent breakage
- Ultra tough, tangle-free fabric cable

Supreme comfort

- Ultra soft leather ear cushions for long time wearing
- Self-adjusting inner headband dissipates pressure and heat

Philips O'Neill
THE STRETCH headband
headphone with mic

40mm drivers/closed-back
Over-ear



SHO9565BK



PHILIPS

O'NEILL

THE STRETCH headband headphone with mic
40mm drivers/closed-back Over-ear

Specifications

Connectivity

- Cable Connection: Singled-sided cable
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold plated
- Type of cable: OFC
- Remote and mic compatible with: Blackberry, HTC, iPhone, LG, Motorola, Nokia, Palm, Samsung, Sony Ericsson
- *Track control compatible with: iPhone 3GS, iPhone4
- Cable Connection: one-sided

Convenience

- Volume control

Outer Carton

- EAN: 87 12581 59894 5
- Gross weight: 1.81 kg
- Outer carton (L x W x H): 29.5 x 24.2 x 21.4 cm
- Nett weight: 0.513 kg
- Number of consumer packagings: 3
- Tare weight: 1.297 kg

Packaging dimensions

- Packaging dimensions (W x H x D):

- 19.5 x 21.5 x 9 cm
- EAN: 69 23410 70951 3
- Gross weight: 0.51 kg
- Nett weight: 0.171 kg
- Number of products included: 1
- Packaging type: Carton
- Tare weight: 0.339 kg
- Type of shelf placement: Both

Sound

- Acoustic system: Closed
- Diaphragm: Mylar dome
- Frequency response: 15 - 24 000 Hz
- Impedance: 32 ohm
- Magnet type: Neodymium
- Maximum power input: 100 mW
- Sensitivity: 104 dB
- Speaker diameter: 40 mm
- Type: Dynamic
- Voice coil: CCAW

Product dimensions

- Product dimensions (W x H x D):
17 x 19.5 x 7.5 cm
- Weight: 0.17 kg

SHO9565BK/10

Highlights

40mm neodymium drivers

Rock out to high quality tunes on the go with dynamic 40mm drivers that deliver crystal clear sound coupled with thumping bass.

Built-in mic & remote control

Jump between music and calls with a flick of your finger using the built-in microphone and remote control. It makes staying connected with your music, and the people who matter, a breeze.

L-shaped connector

Enjoy music for longer with a reinforced L-shaped cable connector that makes these headphones more durable and longer lasting.

Over-ear isolating cushions

Be part of the city's buzz but not its noise with over-ear sound isolating cushions. Not only will you enjoy long lasting comfort, these cushions help you hear and enjoy every sonic detail of your favorite tunes.

Self-adjusting inner headband

Stay cool and comfortable with the cleverly constructed, stretchy and lightweight inner headband. Keep your headphones snugly in place no matter how long you wear them.

Super stretchable headband

Twist, stretch and bend the headband without breaking it. Constructed from a high grade nylon TR55 super stretch polymer, these headphones are extremely tough, flexible and ready to stay by your side wherever life takes you.

HEADSET FOR»
MOBILE PHONE
//MUSIC AND CALLS

Issue date 2014-08-13

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Version: 8.2.7

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

12 NC: 8670 000 75299
EAN: 69 23410 70951 3

www.philips.com