



Philips  
Indoor Corded TV  
Headphone

On-ear  
Silver



SHP1800

## Ultra Lightweight + 6m TV cable

For TV

A lightweight headphone for long use, with a 6m cable extension for more freedom of movement and sitting area choice. In addition, bass beat vents provide rich deep sound.

### **The perfect listening experience**

- Bass beat vents allow air movement for better sound

### **You'll forget you're wearing them!**

- Lightweight headband enhances comfort and adds durability
- Comfort is enhanced for long-term use

### **Always ready**

- Headphone specifically made for TV and HiFi equipment
- An ideal length for you to watch TV at distance
- In-line control that simplifies volume adjustment

# PHILIPS

# Specifications

## Product dimensions

- Product dimensions (W x H x D):  
14 x 16 x 4.9 cm
- Weight: 0.1031 kg

## Sound

- Diaphragm: Mylar dome
- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: copper
- Frequency response: 14 - 22 000 Hz
- Impedance: 32 ohm
- Maximum power input: 100 mW
- Sensitivity: 100 dB
- Speaker diameter: 30 mm
- Type: Dynamic

## Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 6 m
- Connector: 3.5 mm
- Finishing of connector: chrome-plated
- Type of cable: copper

## Convenience

- Volume control

## Accessories

- Adaptor plug: 3.5 - 6.3 mm

## Packaging dimensions

- EAN: 87 10895 95704 5
- Number of products included: 1
- Packaging type: Blister
- Type of shelf placement: Both
- Packaging dimensions (W x H x D):  
17.7 x 22.1 x 5.8 cm
- Nett weight: 0.103 kg
- Gross weight: 0.203 kg
- Tare weight: 0.1 kg

## Outer Carton

- EAN: 87 10895 95706 9
- Number of consumer packagings: 48
- Outer carton (L x W x H): 74 x 40.3 x 52.8 cm
- Nett weight: 4.944 kg
- Gross weight: 13.6 kg
- Tare weight: 8.656 kg

## Inner Carton

- EAN: 87 10895 95705 2
- Number of consumer packagings: 6
- Inner carton (L x W x H): 35.7 x 18.9 x 24.9 cm
- Nett weight: 0.618 kg
- Gross weight: 1.504 kg
- Tare weight: 0.886 kg

# Highlights

## Bass Beat vents

Bass beat vents allow air movement for better sound with a deep rich bass.

## Light weight headband

The light weight material used for the headband

## Comfortable to wear

This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.

## TV Headphone

Designed to make TV viewing a more personal experience, this headphone has a longer cable and its own volume control so you can sit further away from the TV. It's great for listening to your HiFi equipment too.

## 6m cable

Extra long 6m cable for you to connect your headphones to TV or any audio equipment.

## In-line volume control

Adjust the volume to your preferred level without having to go to the audio source unit.

