



Philips
Stereo Headphones

40mm drivers/open-back
Over-ear

SHP2000



Superb comfort and fully adjustable

For music, PC, TV

Full-size lightweight headphones with fully adjustable headband and ear shells to provide excellent fit and comfortable listening

You'll forget you're wearing them!

- Ear cushions improve wearing comfort and bass response
- Easy adjustable headband ensures optimum fit and comfort
- Lightweight headband enhances comfort and adds durability

The perfect listening experience

- The whole ear is covered to optimize sound quality

Always ready to go

- A 2m long cable that lets you put the player in your bag

PHILIPS

Specifications

Sound

- Acoustic system: open
- Frequency response: 15 - 22 000 Hz
- Impedance: 32 ohm
- Maximum power input: 50 mW
- Sensitivity: 96 dB
- Speaker diameter: 40 mm
- Frequency response: 10 - 23 000 Hz

Connectivity

- Cable length: 2 m
- Finishing of connector: chrome-plated
- Type of cable: OFC

Accessories

- Adaptor plug: 3.5 - 6.3 mm

Packaging dimensions

- Packaging dimensions (W x H x D):
19.7 x 24.5 x 10.9 cm
- Gross weight: 0.418 kg

- Nett weight: 0.226 kg
- Tare weight: 0.192 kg
- EAN: 87 10895 94585 1
- Number of products included: 1
- Packaging type: Carton

Outer Carton

- Gross weight: 12.76 kg
- Outer carton (L x W x H): 69 x 42.8 x 47.4 cm
- Nett weight: 5.424 kg
- Tare weight: 7.336 kg
- EAN: 87 10895 95734 2
- Number of consumer packagings: 24

Inner Carton

- Gross weight: 2.88 kg
- Inner carton (L x W x H): 40.5 x 33.3 x 22.2 cm
- Nett weight: 2.51 kg
- Tare weight: 0.37 kg
- EAN: 87 10895 95733 5
- Number of consumer packagings: 6

Highlights

Full size design

Full-size earshells of these Philips headphones not only cover your whole ear for better sound quality, but also provide space for a larger, higher performance driver.

Comfort ear cushions

The special shape and luxurious materials used for the ear cushions of these Philips headphones ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

2m cable

The ideal length of cable to give you more freedom of movement and to choose where you carry your audio device.

Easy adjustable headband

The easily adjustable mechanism provides a comfortable close fitting acoustic seal between the ear cushion and ear, ensuring optimal performance.

Light weight headband

The light weight material used for the headband

