



Philips
Stereo Headphones

40mm drivers/open-back
Over-ear

SHP2000



Superb comfort and fully adjustable

For music, PC, TV

Full-size lightweight headphones with fully adjustable headband and ear shells to provide excellent fit and comfortable listening

You'll forget you're wearing them!

- Ear cushions improve wearing comfort and bass response
- Easy adjustable headband ensures optimum fit and comfort
- Lightweight headband enhances comfort and adds durability

The perfect listening experience

- The whole ear is covered to optimize sound quality

Always ready to go

- A 2m long cable that lets you put the player in your bag

PHILIPS

Stereo Headphones
40mm drivers/open-back Over-ear

Specifications

Sound

- Acoustic system: open
- Frequency response: 15 - 22 000 Hz
- Impedance: 32 ohm
- Maximum power input: 50 mW
- Sensitivity: 96 dB
- Speaker diameter: 40 mm
- Frequency response: 10 - 23 000 Hz

Connectivity

- Cable length: 2 m
- Finishing of connector: chrome-plated
- Type of cable: OFC

Accessories

- Adaptor plug: 3.5 - 6.3 mm

Packaging Data

- 12NC: 9082 100 07152
- EAN/UPC/GTIN: 87 10895 94586 8
- Gross weight: 0.418
- Tare weight: 0.192
- Net weight: 0.226

- Length: 196
- Width: 107
- Height: 208

Inner Carton

- EAN/UPC/GTIN: 871089595736 6
- Quantity: 6
- Gross weight: 2.88
- Tare weight: 0.37
- Net weight: 2.51
- Length: 405
- Width: 333
- Height: 222

Outer Carton

- EAN/UPC/GTIN: 87 10895 95735 9
- Quantity: 24
- Gross weight: 12.94
- Tare weight: 2.9
- Length: 681
- Width: 425
- Height: 469
- Net weight: 10

SHP2000/97

Highlights

Full size design

Full-size earshells of these Philips headphones not only cover your whole ear for better sound quality, but also provide space for a larger, higher performance driver.

Comfort ear cushions

The special shape and luxurious materials used for the ear cushions of these Philips headphones ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

2m cable

The ideal length of cable to give you more freedom of movement and to choose where you carry your audio device.

Easy adjustable headband

The easily adjustable mechanism provides a comfortable close fitting acoustic seal between the ear cushion and ear, ensuring optimal performance.

Light weight headband

The light weight material used for the headband



Issue date 2015-06-16

Version: 9.0.11

12 NC: 9082 100 07152
EAN: 87 10895 94586 8

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com