


Philips  
Sports in ear headset



SHQ1017



## Sweat proof

with iPhone remote control and mic

Constructed with antimicrobial and water resistant materials, these headphones have been designed for the fitness enthusiast. The cable length is also customisable making them ideal for use with a sports armband or for general use.

### Innovation for Athletes

- Ultra lightweight design
- A 1.2 m long cable that is ideal for outdoor use
- Ultra-soft silicone caps sit comfortably in your ears

### Designed for active use

- Sweat proof
- Cable clip
- Customised cable length

### Energise you

- Bass thumping stereo sound - fuel for your workout
- Mic and music control


### Supreme comfort

- 3 sizes of ear sleeves for a customised fit

**PHILIPS**  
sense and simplicity

# Highlights

## Sweat proof



Designed with a water resistant seal to protect your headphones from sweat-related damage

## Bass thumping stereo sound

Acoustics finely tuned to enhance the sporting experience - fuel for your workout


## Cable clip



Clip helps fix cable securely



## 3-size ultra-soft silicone caps



The 3 sizes of ultra-soft silicone caps of these Philips earphones sit comfortably in your ears without adding pressure to them whilst blocking out unwanted noise.

## Ultra lightweight design

Ultra lightweight design for a comfortable fit - designed for sports

## 1.2 m cable

The ideal cable length to give you the freedom to put your audio device where you want.

## Customised cable length

The 60 cm short cable is designed for armband use. You may also find your perfect fit by using the 60 cm extension cable.

## Customised fit

Three sizes of soft ear sleeves enable you to customise the Philips headphones to fit your ears.

## Mic and music control

The super sleek microphone and controller allows you to talk, listen and control your iPod/iPhone/iPad remotely.

# Specifications

## Sound

- Diaphragm: Mylar Dome
- Frequency response: 30–20,000 Hz
- Impedance: 16 Ohm
- Maximum power input: 10 mW
- Sensitivity: 110 dB
- Speaker diameter: 13.5 mm
- Type: Dynamic
- Voice coil: CCAW
- Magnet type: Neodymium

## Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: Gold plated
- Type of cable: OFC

## Accessories

- Carrying case

## Packaging dimensions

- Packaging dimensions (W x H x D): 9.5 x 17.5 x 3 cm
- EAN: 69 23410 70891 2
- Number of products included: 1
- Gross weight: 0.074 kg
- Net weight: 0.045 kg
- Packaging type: Blister
- Tare weight: 0.029 kg
- Type of shelf placement: Both

## Outer Carton

- Number of consumer packages: 24
- Gross weight: 2.563 kg
- Outer carton (L x W x H): 39.2 x 23.2 x 25 cm
- Net weight: 1.08 kg
- Tare weight: 1.483 kg
- EAN: 87 12581 59498 5

## Inner Carton

- EAN: 87 12581 59500 5
- Number of consumer packages: 3
- Gross weight: 0.277 kg
- Inner carton (L x W x H): 18.5 x 10.5 x 10.4 cm
- Net weight: 0.135 kg
- Tare weight: 0.142 kg

## Convenience

- Volume control

## Product dimensions

- Product dimensions (W x H x D): 6.5 x 6.5 x 5 cm
- Weight: 0.045 kg

## iPad compatibility

- Compatible with: iPad, iPad 2

## iPhone compatibility

- Compatible with: iPhone 3GS, iPhone 4, iPhone 4S



Issue date 2013-01-10

Version: 4.1.6

12 NC: 8670 000 74604  
EAN: 69 23410 70891 2

© 2013 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)