



Philips ActionFit  
Sports headphones with  
mic

8.6mm drivers/open-back  
Earbud

SHQ1305LF

## Experience freedom. Stop at nothing

Secure fit and ultra lightweight

Hit a new personal record with the featherweight Actionfit SHQ1305 headphones. Sweat and rain proof, these tough headphones guarantee powerful bass and an optimal fit, thanks to high performance drivers and a C shaped stability lock.

### Intensity

- High performance sound drives peak performance
- Open acoustic design lets you be aware of your surroundings

### Freedom

- 5.7g ultra lightweight design provides ultimate comfort\*
- C-shaped ear tip secures the headphones in place
- 3 ear tip sizes for the optimum fit
- Cable clip included for tangle-free workout

### protection

- Kevlar® Reinforced cable for ultimate durability
- Sweat and moisture proof – ideal for any workout
- Sporty carrying pouch for easy storage

### Simply stay connected

- Remote control and mic for switching from music to call



reddot award 2015  
winner

# PHILIPS

Sports headphones with mic  
8.6mm drivers/open-back Earbud

SHQ1305LF/00


# Highlights

## 3 choices of ear tips sizes




3 ear tip sizes for the optimum fit

## 5.7g ultra lightweight design\*



Weighing in at just 5.7g, these Actionfit sports earphones are so light and comfortable that you will forget you are even wearing them. Perfect for keeping you going right through the hard final miles.

## Cable clip



A cable clip comes included with ActionFit earphones, keeping the cable out of your way while you push yourself harder.

## Sporty carrying pouch for easy

Sporty carrying pouch for easy storage

## C-shaped stabilizing ear tip




C-shaped rubberized ear tips keep the Actionfit earphones tightly in your ear so you can focus on your workout, not on keeping them in.

## Hands free call



Remote control and mic for switching from music to call

## High performance sound




8.6mm neodymium drivers pump out high performance sound, pushing you to perform at your best.

## Kevlar® Reinforced cable



Kevlar® reinforced headphone cables are tough enough to survive even the roughest of workouts.

## Open acoustic design



These ActionFit headphones do not block out sound, so you can keep aware of your environment and stay safe, especially when exercising outdoors. An open acoustic platform provides quality sound without masking the world around you.

# Specifications

## Sound

- Diaphragm: PET
- Frequency response: 15 - 22 000 Hz
- Impedance: 32 Ohm
- Sensitivity: 107 dB
- Maximum power input: 10 mW
- Speaker diameter: 13.6 mm
- Acoustic system: Semi-closed
- Magnet type: Neodymium

## Design

- Color: Lime Yellow & White

## Connectivity

- Connector: 3.5 mm
- Cable length: 1.2 m
- Cable Connection: two-parallel, symmetric
- Finishing of connector: Gold plated

## Accessories

- Storage pouch
- Cable management: Cable clip

## Packaging dimensions

- EAN: 69 25970 70528 8
- Packaging dimensions (W x H x D):  
9.5 x 17.5 x 2.5 cm

- Gross weight: 0.0584 kg
- Nett weight: 0.0244 kg
- Number of products included: 1
- Packaging type: Blister
- Tare weight: 0.034 kg
- Type of shelf placement: Both

## Inner Carton

- Gross weight: 0.2062 kg
- GTIN: 2 69 25970 70528 2
- Inner carton (L x W x H): 18 x 8.2 x 10.5 cm
- Nett weight: 0.0732 kg
- Number of consumer packagings: 3
- Tare weight: 0.133 kg

## Outer Carton

- Gross weight: 1.9326 kg
- GTIN: 1 69 25970 70528 5
- Outer carton (L x W x H): 38 x 18.1 x 24.8 cm
- Nett weight: 0.5856 kg
- Number of consumer packagings: 24
- Tare weight: 1.347 kg

## Product dimensions

- Product dimensions (W x H x D): 3 x 8 x 2.8 cm
- Weight: 0.0244 kg



Issue date 2017-03-16

Version: 1.0.3

12 NC: 8670 001 26971  
EAN: 69 25970 70528 8

© 2017 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)