




Philips ActionFit  
Sports ear hook  
headphones

**ActionFit**  
Orange and Grey

**SHQ3005**



## Tuned for sports

### Adjustable fit

Constructed with waterproof materials coupled with an anti bacterial agent that helps kill germs, these headphones have been designed for the fitness enthusiast

#### **Innovation for Athletes**

- Customisable ear hooks
- Ultra-soft silicone caps sit comfortably in your ears
- A 1.2 m long cable that is ideal for outdoor use

#### **Designed for active use**

- Washable
- Sweat proof
- Cable clip

#### **Energise you**

- Bass thumping stereo sound - fuel for your workout
- Sound Isolation headphones to minimise environmental noise

# PHILIPS

# Highlights

## Washable



Constructed with waterproof materials allowing you to wash your headphones under running tap water

## Sweat proof



Designed with a water resistant seal to protect your headphones from sweat-related damage

## Customisable ear hooks




Customisable ear hooks for enhanced fit - designed for sports

## Bass thumping stereo sound

Acoustics finely tuned to enhance the sporting experience - fuel for your workout

## 3-size ultra-soft silicone caps



The 3 sizes of ultra-soft silicone caps of these Philips earphones sit comfortably in your ears without adding pressure to them whilst blocking out unwanted noise.

## Cable clip



Clip helps fix cable securely

## Sound Isolation



With sound isolation, you will hear and enjoy greater music details at a lower volume than is possible with normal headphones. Based on a thorough understanding of the human ear canal anatomy, the sound isolation earphone's angled acoustic design creates a perfect seal between the ambient sound source and the ear canal, thus eliminating unwanted background noise while delivering sound directly to your ears. Even at a moderate volume setting, you can still discern music details without noise distractions from the environment. Earphone sleeves are available in three sizes to provide the best fit.

## 1.2 m cable

The ideal cable length to give you the freedom to put your audio device where you want.

# Specifications

## Sound

- Diaphragm: Mylar dome
- Frequency response: 15–22,000 Hz
- Impedance: 16 ohm
- Magnet type: Neodymium
- Maximum power input: 20 mW
- Sensitivity: 102 dB
- Speaker diameter: 9 mm
- Type: Dynamic
- Voice coil: CCAW

## Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: Gold-plated
- Type of cable: OFC

## Accessories

- Included: transport case

## Packaging dimensions

- Packaging dimensions (W x H x D):  
9.5 x 17.5 x 3.5 cm
- Net weight: 0.024 kg
- Gross weight: 0.075 kg

- Tare weight: 0.051 kg
- EAN: 87 12581 63853 5
- Number of products included: 1
- Packaging type: Carton
- Type of shelf placement: Both

## Outer Carton

- Outer carton (L x W x H): 38.8 x 25.6 x 24.8 cm
- Net weight: 0.576 kg
- Gross weight: 2.587 kg
- Tare weight: 2.011 kg
- Number of consumer packages: 24
- GTIN: 1 87 12581 63853 2

## Inner Carton

- Inner carton (L x W x H): 18.3 x 11.7 x 10.4 cm
- Net weight: 0.072 kg
- Gross weight: 0.27 kg
- Tare weight: 0.198 kg
- Number of consumer packages: 3
- GTIN: 2 87 12581 63853 9

## Product dimensions

- Product dimensions (W x H x D):  
3.95 x 6.35 x 2.4 cm
- Weight: 0.024 kg



Issue date 2014-09-26

Version: 1.1.4

12 NC: 8670 000 88116  
EAN: 87 12581 63853 5

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)