




Philips  
Earhook Headphones

ActionFit  
Orange & Grey

SHQ3005



## Tuned for sports

with adjustable fit

Constructed with water proof materials coupled with an anti bacterial agent that helps kill germs, these headphones have been designed for the fitness enthusiast

### Innovation for Athletes

- Customizable ear hooks
- Ultra-soft silicon caps sit comfortably in your ears
- A 1.2m long cable that is ideal for outdoor use

### Designed for active use

- Washable
- Sweat proof
- Cable clip

### Energize you

- Bass thumping stereo sound - fuel for your workout
- Sound Isolation headphones to minimize environmental noise

# PHILIPS

# Highlights

## Washable



Constructed with water proof materials allowing you to wash your headphones under running tap water

## Sweat proof



Designed with a water resistant seal to protect your headphones from sweat related damage

## Customizable ear hooks




Customizable ear hooks for enhanced fit - designed for sports

## Bass thumping stereo sound

Acoustics finely tuned to enhance the sporting experience - fuel for your workout

## 3-size ultra-soft silicon caps



The 3 sizes of ultra-soft silicon caps of these Philips earphones sit comfortably in your ears without adding pressure to them whilst blocking out unwanted noise.

## Cable clip



Clip helps fix cable securely

## Sound Isolation



With sound isolation, you will hear and enjoy greater music details at a lower volume than is possible with normal headphones. Based on thorough understanding of the human ear canal anatomy, the sound isolation earphone's angled acoustic design creates a perfect seal between the ambient sound source and the ear canal, thus eliminating unwanted background noise while delivering sound directly to your ears. Even at a moderate volume setting, you can still discern music details without noise distractions from the environment. Earphone sleeves are available in three sizes to provide the best fit.

## 1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

# Specifications

## Sound

- Diaphragm: Mylar dome
- Frequency response: 15 - 22 000 Hz
- Impedance: 16 ohm
- Magnet type: Neodymium
- Maximum power input: 20 mW
- Sensitivity: 102 dB
- Speaker diameter: 9 mm
- Type: Dynamic
- Voice coil: CCAW

## Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC

## Accessories

- Included: transport case

## Packaging dimensions

- Packaging dimensions (W x H x D):  
9,5 x 17,5 x 3,5 cm
- Nett weight: 0,021 kg
- Gross weight: 0,072 kg
- Tare weight: 0,051 kg
- Number of products included: 1
- Packaging dimensions (W x H x D):  
3,7 x 6,9 x 1,4 inch
- Gross weight: 0,159 lb
- Nett weight: 0,046 lb
- Tare weight: 0,113 lb
- UPC: 6 09585 22537 4

- Packaging type: Dummy
- Type of shelf placement: Dummy

## Outer Carton

- Outer carton (L x W x H): 38,8 x 25,6 x 24,8 cm
- Nett weight: 0,504 kg
- Gross weight: 2,514 kg
- Tare weight: 2,010 kg
- Number of consumer packagings: 24
- Gross weight: 5,542 lb
- Outer carton (L x W x H): 15,3 x 10,1 x 9,8 inch
- Nett weight: 1,111 lb
- Tare weight: 4,431 lb
- GTIN: 1 06 09585 22537 1

## Inner Carton

- Inner carton (L x W x H): 18,3 x 11,7 x 10,4 cm
- Nett weight: 0,063 kg
- Gross weight: 0,26 kg
- Tare weight: 0,197 kg
- Number of consumer packagings: 3
- Gross weight: 0,573 lb
- Inner carton (L x W x H): 7,2 x 4,6 x 4,1 inch
- Nett weight: 0,139 lb
- Tare weight: 0,434 lb
- GTIN: 2 06 09585 22537 8

## Product dimensions

- Product dimensions (W x H x D):  
1,6 x 2,5 x 0,9 inch
- Product dimensions (W x H x D):  
3,95 x 6,35 x 2,4 cm
- Weight: 0,021 kg
- Weight: 0,046 lb



Issue date 2014-03-14

Version: 1.1.4

12 NC: 8670 000 88119  
UPC: 6 09585 22537 4

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)