

Philips  
Sports earhook headset



SHQ3017



## Sweatproof and Washable

With iPhone remote control and mic

Constructed with antimicrobial and water proof materials, these headphones have been designed for the fitness enthusiast. The cable length is also customizable making them ideal for use with a sports armband or general use.

### Innovation for Athletes

- Customizable ear hooks
- Ultra-soft silicon caps sit comfortably in your ears
- A 1.2m long cable that is ideal for outdoor use

### Designed for active use

- Cable clip
- Sweat proof
- Washable
- Customized cable length

### Energize you

- Bass thumping stereo sound - fuel for your workout
- Mic and music control

### Supreme comfort

- 3 sizes of ear sleeves for a customized fit



# PHILIPS

# Highlights

## Sweat proof



Designed with a water resistant seal to protect your headphones from sweat related damage

## Washable



Constructed with water proof materials allowing you to wash your headphones under running tap water

## Bass thumping stereo sound

Acoustics finely tuned to enhance the sporting experience - fuel for your workout

## Cable clip



Clip helps fix cable securely



## Customizable ear hooks



Customizable ear hooks for enhanced fit - designed for sports

## Customized fit

Three sizes of soft ear sleeves enable you to customize the Philips headphones to fit to your ears.

## 3-size ultra-soft silicon caps



The 3 sizes of ultra-soft silicon caps of these Philips earphones sit comfortably in your ears without adding pressure to them whilst blocking out unwanted noise.

## 1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

## Customized cable length

The 60cm short cable is design for armband use. You may also find your perfect fit by using the 60cm extension cable.

## Mic and music control

The super sleek microphone and controller allows you to talk, listen and control your iPod/iPhone/iPad remotely.

# Specifications

## Sound

- Diaphragm: Mylar Dome
- Frequency response: 15 - 22 000 Hz
- Impedance: 16 Ohm
- Magnet type: Neodymium
- Maximum power input: 20 mW
- Sensitivity: 102 dB
- Speaker diameter: 9 mm
- Type: Dynamic
- Voice coil: CCAW

## Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: Gold plated
- Type of cable: OFC

## Convenience

- Volume control

## Accessories

- Carrying case

## Packaging dimensions

- UPC: 6 09585 21183 4
- Number of products included: 1
- Packaging dimensions (W x H x D): 9.5 x 17.5 x 3.5 cm
- Gross weight: 0.077 kg
- Nett weight: 0.03 kg
- Tare weight: 0.047 kg
- Packaging type: Carton
- Packaging dimensions (W x H x D): 3.7 x 6.9 x 1.4 inch
- Gross weight: 0.170 lb
- Nett weight: 0.066 lb
- Tare weight: 0.104 lb
- Type of shelf placement: Laying

## Outer Carton

- Number of consumer packagings: 24
- Gross weight: 2.635 kg
- Outer carton (L x W x H): 38.8 x 25.6 x 24.8 cm
- Nett weight: 0.72 kg
- Tare weight: 1.915 kg
- GTIN: 1 06 09585 21183 1
- Gross weight: 5.809 lb
- Outer carton (L x W x H): 15.3 x 10.1 x 9.8 inch
- Nett weight: 1.587 lb
- Tare weight: 4.222 lb

## Inner Carton

- Number of consumer packagings: 3
- Gross weight: 0.279 kg
- Inner carton (L x W x H): 18.3 x 11.7 x 10.4 cm
- Nett weight: 0.09 kg
- Tare weight: 0.189 kg
- GTIN: 2 06 09585 21183 8
- Gross weight: 0.615 lb
- Inner carton (L x W x H): 7.2 x 4.6 x 4.1 inch
- Nett weight: 0.198 lb
- Tare weight: 0.417 lb

## iPad compatibility

- Compatible with: iPad 2

## iPhone compatibility

- Compatible with: iPhone 3GS, iPhone 4, iPhone 4S



Issue date 2014-03-14

Version: 4.1.4

12 NC: 8670 000 74613  
UPC: 6 09585 21183 4

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)