

Philips ActionFit
Sports earhook headset

ActionFit
Orange & Grey

SHQ3207



Tuned for Sports

With adjustable earhook for secure fit

With its patented adjustable earhook, the lightweight & sweat-resistant SHQ3200 lets you focus on whatever workout you're doing, without losing motivation. If not for the amazing sound that keeps you going, you'll barely know they're there.

Connect to music and calls

- Switch from music to phone calls with iPhone mic & remote
- Take calls and control your music with iPhone mic and remote

Designed for a secure and comfortable fit

- Patented adjustable ear hook for a secure fit
- 3 choices of ear cap sizes for optimal fit
- Ultrasoft silicon caps sit comfortably in your ears

Designed for high performance

- Kevlar-reinforced cable for ultimate durability
- Reflective stopper in the cable
- Sweat resistant and rain proof – ideal for any workout
- 8gm headphones for superb fit and ultra lightweight comfort

Excellent sound with added bass boost

- Excellent sound generated by 9mm drivers
- Powerful bass to boost motivation

PHILIPS

Highlights

Adjustable ear hook



With its patented adjustable ear hook, ActionFit headphones ensure the ultimate fit that's secure yet comfortable. Just hook the headphones on to your ears and slide the adjustable hook up or down to snugly fit your ear just so. Now you're all set to conquer any workout or terrain – your headphones are staying on, no matter what.

Built in iPhone mic & remote

Switch from music to phone calls with iPhone mic & remote

Excellent sound




ActionFit headphones boast finely tuned 9mm drivers that are specifically designed to generate excellent sound. Sound so pristine and powerful that you'll easily immerse in your workout – and get the most out of your music and moves.

iPhone remote




ActionFit headphones feature a built-in iPhone microphone so you can easily switch from enjoying your music to taking a phone call. Staying connected with your music – and the people who matter most to you – is a real breeze.

Kevlar-reinforced cable



Your ActionFit headphones are specially designed for durability and strength. Its Kevlar-coated cable is well protected against tearing and breaking, and can withstand extreme environments – and workouts.

Powerful bass



There's nothing better than a solid groove to get you into your workout rhythm. With

ActionFit headphones, your grooves are powered by superbly deep and dynamic bass that will boost any routine, letting you take it to a higher level.

Reflective stopper




Reflective stopper in the cable

S, M, L, caps



3 choices of ear cap sizes for optimal fit

Soft silicon caps



Your ActionFit headphones come with ultrasoft silicon ear caps that are specially designed to sit snugly in your ears. They're so comfortable that you may never want to take them out.

Specifications

Packaging dimensions

- Number of products included: 1
- Packaging type: Carton
- UPC: 6 09585 23018 7
- Packaging dimensions (W x H x D): 7.5 x 17.5 x 3.2 cm
- Packaging dimensions (W x H x D): 3.0 x 6.9 x 1.3 inch
- Gross weight: 0.057 kg
- Gross weight: 0.126 lb
- Nett weight: 0.022 kg
- Nett weight: 0.049 lb
- Tare weight: 0.077 lb
- Tare weight: 0.035 kg
- Type of shelf placement: Both

Inner Carton

- GTIN: 2 06 09585 23018 1
- Number of consumer packagings: 3
- Gross weight: 0.204 kg
- Gross weight: 0.450 lb
- Inner carton (L x W x H): 7.1 x 4.1 x 3.3 inch
- Inner carton (L x W x H): 18 x 10.3 x 8.5 cm
- Nett weight: 0.066 kg
- Nett weight: 0.146 lb
- Tare weight: 0.304 lb
- Tare weight: 0.138 kg

Outer Carton

- GTIN: 1 06 09585 23018 4
- Number of consumer packagings: 24
- Gross weight: 1.936 kg
- Gross weight: 4.268 lb
- Outer carton (L x W x H): 15.0 x 8.8 x 8.1 inch
- Outer carton (L x W x H): 38 x 22.3 x 20.6 cm
- Nett weight: 0.528 kg

- Nett weight: 1.164 lb
- Tare weight: 3.104 lb
- Tare weight: 1.408 kg

Product dimensions

- Product dimensions (W x H x D): 1.6 x 2.5 x 0.9 inch
- Product dimensions (W x H x D): 3.95 x 6.35 x 2.4 cm
- Weight: 0.022 kg
- Weight: 0.049 lb

Accessories

- Storage pouch

Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.0 m
- Connector: 3.5 mm
- Finishing of connector: Gold plated
- Type of cable: OFC

Convenience

- Volume control

Sound

- Acoustic system: Closed
- Diaphragm: Mylar dome
- Frequency response: 15 - 22 000 Hz
- Impedance: 16 Ohm
- Maximum power input: 20 mW
- Sensitivity: 102 dB
- Speaker diameter: 9 mm
- Type: Dynamic
- Voice coil: CCAW



Issue date 2014-03-17

Version: 1.2.5

12 NC: 8670 000 96814
EAN: 00 60958 52301 87

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com