



Philips  
Sports earhook headset

**ActionFit**  
Orange and Grey



**SHQ3217**



## Tuned for Sports

With adjustable ear hook for secure fit

With its patented adjustable ear hook, the lightweight and sweat-resistant SHQ3217 lets you focus on whatever workout you're doing, without losing motivation. Apart from the amazing sound keeping you going, you'll barely know they're there.

### Connect to music and calls

- Switch from music to phone calls with iPhone mic and remote

### Designed for a secure and comfortable fit

- Patented adjustable ear hook for a secure fit
- 3 choices of ear cap size for optimal fit
- Ultra-soft silicone caps sit comfortably in your ears

### Designed for high performance

- Cable clip and protective pouch for easy use and storage
- Kevlar-reinforced cable for ultimate durability
- Reflective stopper in the cable
- Sweat-resistant and rain-proof – ideal for any workout
- 8-g headphones for superb fit and ultra-lightweight comfort

### Excellent sound with added bass boost

- Excellent sound generated by 9-mm drivers
- Powerful bass to boost motivation

# PHILIPS

# Highlights

## Adjustable ear hook



With their patented adjustable ear hook, ActionFit headphones ensure the ultimate fit that's secure yet comfortable. Just hook the headphones onto your ears and slide the adjustable hook up or down to snugly fit your ear. Now you're all set to conquer any workout or terrain – your headphones are staying on, no matter what.


## Built-in iPhone mic and remote

Switch from music to phone calls with iPhone mic and remote

## Clip and pouch

ActionFit headphones come with their own clip and pouch for easy cable management and safe storage. Enjoy a tangle-free workout with the clip, then stash your headphones in the breathable pouch. Don't sweat it!

## Excellent sound




ActionFit headphones boast finely tuned 9-mm drivers that are specifically designed to generate excellent sound. Sound so pristine and powerful that you'll easily immerse yourself in your workout – and get the most out of your music and moves.

## Kevlar-reinforced cable



Your ActionFit headphones are specially designed for durability and strength. Their Kevlar-coated cable is well protected against tearing and breaking, and can withstand extreme environments – and workouts.

## Powerful bass



There's nothing better than a solid groove to get you into your workout rhythm. With ActionFit headphones, your grooves are powered by superbly deep and dynamic bass that will boost any routine, letting you take it to a higher level.

## Reflective stopper




Reflective stopper in the cable

## S, M, L caps




3 choices of ear cap size for optimal fit

## Soft silicone caps



Your ActionFit headphones come with ultra-soft silicone ear caps that are specially designed to sit snugly in your ears. They're so comfortable that you may never want to take them out.

## Sweat- and rain-resistant



ActionFit headphones are specially designed for any active lifestyle. Whatever your sport or workout preference, your headphones can handle the heat, wet and sweat! Crafted with premium water-resistant materials, your headphones are comfortable, sweat-proof and rain-proof.

# Specifications

## Packaging dimensions

- EAN: 69 23410 71656 6
- Number of products included: 1
- Packaging type: Soother
- Packaging dimensions (W x H x D): 9.5 x 17.5 x 2.5 cm
- Gross weight: 0.0566 kg
- Net weight: 0.0228 kg
- Tare weight: 0.0338 kg
- Type of shelf placement: Soother

## Inner Carton

- Gross weight: 0.203 kg
- GTIN: 2 69 23410 71656 0
- Inner carton (L x W x H): 18 x 8.2 x 10.5 cm
- Net weight: 0.0684 kg
- Number of consumer packages: 3
- Tare weight: 0.1346 kg

## Outer Carton

- Gross weight: 1.91 kg
- GTIN: 1 69 23410 71656 3
- Outer carton (L x W x H): 38 x 18.1 x 24.8 cm
- Net weight: 0.5472 kg
- Number of consumer packages: 24
- Tare weight: 1.3628 kg

## Product dimensions

- Product dimensions (W x H x D): 5 x 9 x 2.8 cm
- Weight: 0.0228 kg

## Accessories

- Included: transport case

## Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: Gold-plated
- Type of cable: OFC

## Sound

- Diaphragm: Mylar dome
- Frequency response: 15–22,000 Hz
- Impedance: 16 ohm
- Magnet type: Neodymium
- Maximum power input: 20 mW
- Sensitivity: 102 dB
- Speaker diameter: 9 mm
- Type: Dynamic
- Voice coil: CCAW



Issue date 2015-02-20

Version: 2.1.6

12 NC: 8670 000 93015  
EAN: 06 92341 07165 66

© 2015 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)