



Philips  
Sports earhook headset

ActionFit  
Orange & Grey



SHQ3217



## Tuned for Sports

With adjustable earhook for secure fit

With its patented adjustable earhook, the lightweight & sweat-resistant SHQ3217 lets you focus on whatever workout you're doing, without losing motivation. If not for the amazing sound that keeps you going, you'll barely know they're there.

### Connect to music and calls

- Switch from music to phone calls with iPhone mic & remote

### Designed for a secure and comfortable fit

- Patented adjustable ear hook for a secure fit
- 3 choices of ear cap sizes for optimal fit
- Ultrasoft silicon caps sit comfortably in your ears

### Designed for high performance

- Cable clip and protective pouch for easy use and storage
- Kevlar-reinforced cable for ultimate durability
- Reflective stopper in the cable
- Sweat resistant and rain proof – ideal for any workout
- 8gm headphones for superb fit and ultra lightweight comfort

### Excellent sound with added bass boost

- Excellent sound generated by 9mm drivers
- Powerful bass to boost motivation

# PHILIPS

# Highlights

## Adjustable ear hook



With its patented adjustable ear hook, ActionFit headphones ensure the ultimate fit that's secure yet comfortable. Just hook the headphones on to your ears and slide the adjustable hook up or down to snugly fit your ear just so. Now you're all set to conquer any workout or terrain – your headphones are staying on, no matter what.

## Built in iPhone mic & remote

Switch from music to phone calls with iPhone mic & remote

## Clip and pouch

ActionFit headphones come with its own clip and pouch for easy cable management and safe storage. Enjoy a tangle-free workout with the clip, then stash your headphones in the breathable pouch. Don't sweat it!

## Excellent sound




ActionFit headphones boast finely tuned 9mm drivers that are specifically designed to generate excellent sound. Sound so pristine and powerful that you'll easily immerse in your workout – and get the most out of your music and moves.

## Kevlar-reinforced cable



Your ActionFit headphones are specially designed for durability and strength. Its Kevlar-coated cable is well protected against tearing and breaking, and can withstand extreme environments – and workouts.

## Powerful bass



There's nothing better than a solid groove to get you into your workout rhythm. With ActionFit headphones, your grooves are powered by superbly deep and dynamic bass that will boost any routine, letting you take it to a higher level.

## Reflective stopper




Reflective stopper in the cable

## S, M, L, caps




3 choices of ear cap sizes for optimal fit

## Soft silicon caps



Your ActionFit headphones come with ultrasoft silicon ear caps that are specially designed to sit snugly in your ears. They're so comfortable that you may never want to take them out.

## Sweat and rain resistant



ActionFit headphones are specially designed for any active lifestyle. Whatever your sports or workout preference, your headphones can handle the heat, wet and sweat! Crafted with premium water-resistant materials, your headphones are comfortable sweat- and rain-proof.

# Specifications

## Packaging dimensions

- Number of products included: 1
- Packaging type: Carton
- Packaging dimensions (W x H x D):  
3.7 x 6.9 x 1 inch
- Packaging dimensions (W x H x D):  
9.5 x 17.5 x 2.5 cm
- Gross weight: 0.13 lb
- Gross weight: 0.059 kg
- Nett weight: 0.049 lb
- Nett weight: 0.022 kg
- Tare weight: 0.081 lb
- Tare weight: 0.037 kg
- Type of shelf placement: Both
- UPC: 6 09585 22847 4

## Inner Carton

- Gross weight: 0.463 lb
- Gross weight: 0.21 kg
- GTIN: 2 06 09585 22847 8
- Inner carton (L x W x H): 18 x 8.2 x 10.5 cm
- Inner carton (L x W x H): 7.1 x 3.2 x 4.1 inch
- Nett weight: 0.146 lb
- Nett weight: 0.066 kg
- Number of consumer packagings: 3
- Tare weight: 0.317 lb
- Tare weight: 0.144 kg

## Outer Carton

- Gross weight: 4.328 lb
- Gross weight: 1.963 kg
- GTIN: 1 06 09585 22847 1
- Outer carton (L x W x H): 38 x 18.1 x 24.5 cm
- Outer carton (L x W x H): 15 x 7.1 x 9.6 inch

- Nett weight: 1.164 lb
- Nett weight: 0.528 kg
- Number of consumer packagings: 24
- Tare weight: 3.164 lb
- Tare weight: 1.435 kg

## Product dimensions

- Product dimensions (W x H x D):  
1.6 x 2.5 x 0.9 inch
- Product dimensions (W x H x D):  
3.95 x 6.35 x 2.4 cm
- Weight: 0.022 kg
- Weight: 0.049 lb

## Accessories

- Included: transport case

## Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC

## Sound

- Diaphragm: Mylar dome
- Frequency response: 15 - 22 000 Hz
- Impedance: 16 ohm
- Magnet type: Neodymium
- Maximum power input: 20 mW
- Sensitivity: 102 dB
- Speaker diameter: 9 mm
- Type: Dynamic
- Voice coil: CCAW



Issue date 2014-03-14

Version: 2.0.3

12 NC: 8670 000 93356  
UPC: 6 09585 22847 4

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)