



Philips
Sports earhook headset

ActionFit
Orange & Grey



SHQ3217



Tuned for Sports

With adjustable earhook for secure fit

With adjustable earhook, the lightweight & sweat-resistant SHQ3217 headphones lets you focus on whatever workout you're doing, without losing motivation. If not for the amazing sound that keeps you going, you'll barely know they're there.

Connect to music and calls

- Switch from music to phone calls with iPhone mic & remote

Designed for a secure and comfortable fit

- Patented adjustable ear hook for a secure fit
- 3 choices of ear cap sizes for optimal fit
- Ultrasoft silicon caps sit comfortably in your ears

Designed for high performance

- Cable clip and protective pouch for easy use and storage
- Kevlar-reinforced cable for ultimate durability
- Reflective stopper in the cable
- Sweat resistant and rain proof – ideal for any workout
- 8gm headphones for superb fit and ultra lightweight comfort

Excellent sound with added bass boost

- Excellent sound generated by 9mm drivers
- Powerful bass to boost motivation

PHILIPS

Sports earhook headset
ActionFit Orange & Grey

Highlights

Adjustable ear hook



With its patented adjustable ear hook, ActionFit headphones ensure the ultimate fit that's secure yet comfortable. Just hook the headphones on to your ears and slide the adjustable hook up or down to snugly fit your ear just so. Now you're all set to conquer any workout or terrain – your headphones are staying on, no matter what.

Built in iPhone mic & remote

Switch from music to phone calls with iPhone mic & remote

Clip and pouch

ActionFit headphones come with its own clip and pouch for easy cable management and safe storage. Enjoy a tangle-free workout with the clip, then stash your headphones in the breathable pouch. Don't sweat it!

Excellent sound




ActionFit headphones boast finely tuned 9mm drivers that are specifically designed to generate excellent sound. Sound so pristine and powerful that you'll easily immerse in your workout – and get the most out of your music and moves.

Kevlar-reinforced cable



Your ActionFit headphones are specially designed for durability and strength. Its Kevlar-coated cable is well protected against tearing and breaking, and can withstand extreme environments – and workouts.

Powerful bass



There's nothing better than a solid groove to get you into your workout rhythm. With ActionFit headphones, your grooves are powered by superbly deep and dynamic bass that will boost any routine, letting you take it to a higher level.

Reflective stopper



Reflective stopper in the cable


SHQ3217/98

S, M, L, caps




3 choices of ear cap sizes for optimal fit

Soft silicon caps



Your ActionFit headphones come with ultrasoft silicon ear caps that are specially designed to sit snugly in your ears. They're so comfortable that you may never want to take them out.

Sweat and rain resistant



ActionFit headphones are specially designed for any active lifestyle. Whatever your sports or workout preference, your headphones can handle the heat, wet and sweat! Crafted with premium water-resistant materials, your headphones are comfortable sweat- and rain-proof.

Specifications

Packaging dimensions

- EAN: 69 23410 71705 1
- Number of products included: 1
- Packaging type: Dummy
- Packaging dimensions (W x H x D): 9,5 x 17,5 x 2,5 cm
- Gross weight: 0,0566 kg
- Nett weight: 0,0228 kg
- Tare weight: 0,0338 kg
- Type of shelf placement: Dummy

Inner Carton

- Gross weight: 0,2028 kg
- GTIN: 2 69 23410 71705 5
- Inner carton (L x W x H): 18 x 8,2 x 10,5 cm
- Nett weight: 0,0684 kg
- Number of consumer packagings: 3
- Tare weight: 0,1344 kg

Outer Carton

- Gross weight: 1,91 kg
- GTIN: 1 69 23410 71705 8
- Outer carton (L x W x H): 38 x 18,1 x 24,8 cm
- Nett weight: 0,5472 kg
- Number of consumer packagings: 24
- Tare weight: 1,3628 kg

Product dimensions

- Product dimensions (W x H x D): 5 x 9 x 2,8 cm
- Weight: 0,0228 kg

Accessories

- Included: transport case

Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC

Sound

- Diaphragm: Mylar dome
- Frequency response: 15 - 22 000 Hz
- Impedance: 16 ohm
- Magnet type: Neodymium
- Maximum power input: 20 mW
- Sensitivity: 102 dB
- Speaker diameter: 9 mm
- Type: Dynamic
- Voice coil: CCAW



Issue date 2015-04-09

Version: 2.1.7

12 NC: 8670 000 93357
EAN: 69 23410 71705 1

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com