

Philips ActionFit
Sports neckband headset

ActionFit
Orange & Grey

SHQ4207



Tuned for Sports

Lightweight and flexible for secure fit

The featherweight SHQ4207 is crafted from ultra light, flexible and sweat-resistant rubber, ensuring such a perfect fit that you won't want to take it off after your workout. Plus, superb deep bass sound keeps you motivated - always.

Connect to music and calls

- Take calls and control your music with iPhone mic and remote

Designed for a secure and comfortable fit

- Flexible neckband auto-adjusts to your head for perfect fit
- 3 choices of ear cap sizes for optimal fit
- Ultrasoft silicon caps sit comfortably in your ears

Designed for high performance

- Cable clip and protective pouch for easy use and storage
- Kevlar-reinforced cable for ultimate durability
- Reflective stopper in the cable
- Sweat resistant and rain proof – ideal for any workout
- 16gm headphones for superb fit and ultra lightweight comfort

Excellent sound with added bass boost

- Excellent sound generated by 9mm drivers
- Powerful bass to boost motivation

PHILIPS

Highlights

Clip and pouch


ActionFit headphones come with its own clip and pouch for easy cable management and safe storage. Enjoy a tangle-free workout with the clip, then stash your headphones in the breathable pouch. Don't sweat it!

Excellent sound



ActionFit headphones boast finely tuned 9mm drivers that are specifically designed to generate excellent sound. Sound so pristine and powerful that you'll easily immerse in your workout – and get the most out of your music and moves.

Flexible neckband




The neckband of your ActionFit headphones is crafted with supple spring-wire that is designed to fit you naturally and optimally. Its lightweight rubberized earhooks and elastic rubber neckband feel secure yet comfortable throughout any workout.

iPhone remote




ActionFit headphones feature a built-in iPhone microphone so you can easily switch from enjoying your music to taking a phone call. Staying connected with your music – and the people who matter most to you – is a real breeze.

Kevlar-reinforced cable



Your ActionFit headphones are specially designed for durability and strength. Its Kevlar-coated cable is well protected against tearing and breaking, and can withstand extreme environments – and workouts.

Powerful bass



There's nothing better than a solid groove to get you into your workout rhythm. With

ActionFit headphones, your grooves are powered by superbly deep and dynamic bass that will boost any routine, letting you take it to a higher level.

Reflective stopper




Reflective stopper in the cable

S, M, L, caps



3 choices of ear cap sizes for optimal fit

Soft silicon caps



Your ActionFit headphones come with ultrasoft silicon ear caps that are specially designed to sit snugly in your ears. They're so comfortable that you may never want to take them out.

Specifications

Packaging dimensions

- UPC: 6 09585 23017 0
- Number of products included: 1
- Packaging type: Blister
- Packaging dimensions (W x H x D): 15.7 x 20 x 4.5 cm
- Packaging dimensions (W x H x D): 6.2 x 7.9 x 1.8 inch
- Gross weight: 0.114 kg
- Gross weight: 0.251 lb
- Nett weight: 0.017 kg
- Nett weight: 0.037 lb
- Tare weight: 0.214 lb
- Tare weight: 0.097 kg
- Type of shelf placement: Both

Outer Carton

- GTIN: 1 06 09585 23017 7
- Number of consumer packagings: 3
- Gross weight: 0.502 kg
- Gross weight: 1.107 lb
- Outer carton (L x W x H): 6.9 x 6.1 x 8.9 inch
- Outer carton (L x W x H): 17.5 x 15.5 x 22.5 cm
- Nett weight: 0.051 kg
- Nett weight: 0.112 lb
- Tare weight: 0.994 lb
- Tare weight: 0.451 kg

Accessories

- Storage pouch

Connectivity

- Cable Connection: single sided
- Cable length: 1.0 m
- Connector: 3.5 mm
- Finishing of connector: Gold plated
- Type of cable: OFC

Convenience

- Volume control

Product dimensions

- Product dimensions (W x H x D): 4.7 x 5.5 x 1.7 inch
- Product dimensions (W x H x D): 12 x 14 x 4.3 cm
- Weight: 0.017 kg
- Weight: 0.037 lb

Sound

- Acoustic system: Closed
- Diaphragm: Mylar dome
- Frequency response: 15 - 22 000 Hz
- Impedance: 16 Ohm
- Maximum power input: 20 mW
- Sensitivity: 102 dB
- Speaker diameter: 9 mm
- Type: Dynamic
- Voice coil: CCAW



Issue date 2014-03-14

Version: 1.3.2

12 NC: 8670 000 96811
EAN: 00 60958 52301 70

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com