

Philips  
Ear hook Headphones

Black

SHS3200



## Secure fit

Flexible ear hook fits all ears

Ultra-comfortable for active use, these ergonomic ear hook headphones bring fantastic quality music reproduction straight to your ears.

### Music to your ears

- Bass pipe emphasises low tones for a clear, realistic sound
- Enjoy best-in-class performance and optimum sound quality

### Made to fit you and your lifestyle

- 15 mm speaker driver optimises wearing comfort
- 3D flexible ear hook ensures secure fit in all ear sizes
- Ergonomically shaped headphone enhances user comfort
- Contoured ear hook increases wearing comfort and stability

### Always ready to go

- A 1.2 m long cable that is ideal for outdoor use
- Stays comfortably in your ear when you are on the move
- Extremely durable construction extends product life

# PHILIPS

# Specifications

## Product dimensions

- Product dimensions (W x H x D):  
3.5 x 6.1 x 1.8 cm
- Weight: 0.0175 kg

## Sound

- Acoustic system: open
- Magnet type: Neodymium
- Diaphragm: Mylar dome
- Voice coil: copper
- Frequency response: 20 - 20,000 Hz
- Impedance: 16 ohm
- Maximum power input: 15 mW
- Sensitivity: 100 dB
- Speaker diameter: 15 mm
- Type: Dynamic

## Design

- Colour: Black

## Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: chrome-plated
- Type of cable: OFC

## Inner Carton

- Gross weight: 0.1782 kg
- Inner carton (L x W x H): 18.2 x 8.6 x 11 cm
- Net weight: 0.0525 kg
- Tare weight: 0.1257 kg
- EAN: 87 12581 49767 5
- Number of consumer packages: 3

## Outer Carton

- Gross weight: 1.74 kg
- Outer carton (L x W x H): 35.4 x 19.2 x 23.2 cm
- Net weight: 0.42 kg
- Tare weight: 1.32 kg
- EAN: 87 12581 49768 2
- Number of consumer packages: 24

## Packaging dimensions

- Type of shelf placement: Hanging
- Packaging dimensions (W x H x D):  
9.5 x 17 x 2.6 cm
- Gross weight: 0.0452 kg
- Net weight: 0.0175 kg
- Tare weight: 0.0277 kg
- EAN: 87 12581 49766 8
- Number of products included: 1
- Packaging type: Blister

# Highlights

## Bass Pipe

Thanks to an acoustically-tuned air channel that turbo-charges the bass notes, you can enjoy fantastic realism and a truly involved listening experience.

## Excellent sound quality

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance.

## 15 mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.

## 3D Flex Soft ear hook

This 3D ear hook is both soft and flexible, so it stays comfortably in place when you're active or enjoying your music on the move.

## Comfort fit

This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.

## Contoured ear hook

The ear hook stays put behind your ear even when you're on the move, keeping the earphone comfortably in place and sounding great. The ear hook is the part that is in contact with the back of your ears and keeps the headphones on your ears

## 1.2 m cable

The ideal cable length to give you the freedom to put your audio device where you want.

## Designed for active use

Whether you are out running, cycling or taking part in any active pastime, this headphone will stay comfortably in your ear.

## Extremely durable

You can be sure that the product will have an extra-long life thanks to its design, which allows it to withstand knocks and rough use, and the fact that it is made from strong materials.

