

Philips
Headphones

15mm drivers/open-back
Earhook

SHS3200



Secure fit

Flexible earhook fits all ears

Ultra-comfortable for active use, these ergonomic earhook headphones bring fantastic quality music reproduction straight to your ears.

Music to your ears

- Bass pipe emphasizes low tones for a clear, realistic sound
- Enjoy best-in-class performance and optimum sound quality

Made to fit you and your lifestyle

- 15mm speaker driver optimizes wearing comfort
- 3D flexible earhook ensures secure fit in all ear sizes
- Ergonomically-shaped headphone enhances user comfort
- Contoured earhook increase wearing comfort and stability

Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- Stays comfortably in your ear when you are on the move
- Extremely durable construction extends product life

PHILIPS

Specifications

Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: copper
- Diaphragm: Mylar dome
- Frequency response: 20 - 20 000 Hz
- Impedance: 16 ohm
- Maximum power input: 15 mW
- Sensitivity: 100 dB
- Speaker diameter: 15 mm
- Type: Dynamic

Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: chrome-plated
- Type of cable: OFC

Inner Carton

- Gross weight: 1.047 lb
- Inner carton (L x W x H): 7.2 x 7.1 x 4.6 inch
- Nett weight: 0.238 lb
- Tare weight: 0.809 lb
- GTIN: 1 00 26616 02882 2
- Number of consumer packagings: 6

Outer Carton

- Gross weight: 9.921 lb
- Outer carton (L x W x H): 15.4 x 15 x 10.9 inch
- Nett weight: 1.905 lb
- Tare weight: 8.016 lb
- GTIN: 2 00 26616 02882 9
- Number of consumer packagings: 48

Packaging dimensions

- Packaging dimensions (W x H x D): 3.9 x 6.9 x 1 inch
- Gross weight: 0.11 lb
- Nett weight: 0.04 lb
- Tare weight: 0.07 lb
- Number of products included: 1
- Packaging type: Blister
- UPC: 0 26616 02882 5
- Type of shelf placement: Hanging

Product dimensions

- Product dimensions (W x H x D): 1.4 x 2.4 x 0.7 inch
- Weight: 0.040 lb

Highlights

Bass Pipe

Thanks to an acoustically-tuned air channel that turbo-charges the bass notes, you enjoy fantastic realism and a truly involved listening experience.

Excellent sound quality

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance.

15 mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.

3D Flex Soft earhook

This 3D earhook is both soft and flexible, so it stays comfortably in place when you're active or enjoying your music on the move.

Comfort fit

This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.

Contoured earhook

The earhook stays put behind your ear even when you're on the move, keeping the earphone comfortably in place and sounding great. It's the part contacting the back of your ears and keep the headphones on your ears.

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Designed for active use

Whether you are out running, cycling or taking part in any active pastime, this headphone will stay comfortably in your ear.

Extremely durable

Thanks to being designed to take the knocks of rough use and being made from strong materials, you can be sure of an extra long product life.



Issue date 2015-05-22

Version: 9.0.8

12 NC: 9082 100 06528
UPC: 0 26616 02882 5

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com