

Philips
Earclip Headphones

SHS3800



Mix and Match

Enjoy the bass beat sound of ear-clip headphones that designed for comfort, stability and performance.

Music to your ears

- 27mm speaker driver delivers big sound performance
- Bass beat vents allow air movement for better sound
- Neodymium magnet enhances bass performance and sensitivity

Made to fit you and your lifestyle

- Ear cushions improve wearing comfort and bass response
- Contoured earhook increase wearing comfort and stability
- Asymmetric cable keeps the cable out the way
- 3 sets of interchangeable caps to mix and match any style
- Soft ear pads for ultimate lasting comfort

Always ready to go

- A 1.2m long cable that is ideal for outdoor use

PHILIPS
sense and simplicity

Specifications

Inner Carton

- Inner carton (L x W x H): 18,5 x 10,5 x 10,4 cm
- Nett weight: 0,087 kg
- Gross weight: 0,277 kg
- Tare weight: 0,190 kg
- GTIN: 2 87 12581 52642 3
- Number of consumer packagings: 3

Packaging dimensions

- Type of shelf placement: Dummy
- Packaging dimensions (W x H x D): 9,5 x 15 x 3 cm
- Nett weight: 0,029 kg
- Gross weight: 0,079 kg
- Tare weight: 0,05 kg
- EAN: 87 12581 52642 9
- Number of products included: 1
- Packaging type: Dummy

Connectivity

- Cable Connection: two-parallel, asymmetric
- Cable length: 1.2 m
- Connector: 3.5 mm

- Finishing of connector: gold-plated
- Type of cable: copper

Outer Carton

- Outer carton (L x W x H): 39,2 x 23,2 x 25 cm
- Nett weight: 0,696 kg
- Gross weight: 2,738 kg
- Tare weight: 2,042 kg
- EAN: 87 12581 54020 3
- Number of consumer packagings: 24

Sound

- Acoustic system: open
- Diaphragm: Mylar dome
- Frequency response: 12 - 22 000 Hz
- Impedance: 32 ohm
- Magnet type: Neodymium
- Maximum power input: 100 mW
- Sensitivity: 102 dB
- Speaker diameter: 27 mm
- Type: Dynamic
- Voice coil: copper

Highlights

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

27 mm speaker driver

Compact for wearing comfort yet big enough to deliver crisp, powerful sound, the 27 mm speaker driver is a perfect size for non-distorted listening enjoyment.

Asymmetric cabling system

This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.

Bass Beat vents

Bass beat vents allow air movement for better sound with a deep rich bass.

Comfort ear cushions

The special shape and luxurious materials used for the ear cushions of these Philips headphones ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

Contoured earhook

The earhook stays put behind your ear even when you're on the move, keeping the earphone comfortably in place and sounding great. It's the part contacting the back of your ears and keeps the headphones on your ears.

As fashion accessories

Choose one of the three interchangeable earpiece cap sets, each with different styling and colours, to suit your taste and mood.

Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

for ultimate lasting comfort

The ear pads are made of an extra soft foam material which is sensational to the touch and rests gently on your ear. They feel so good that you simply don't want to take them off.



Issue date 2012-07-31

Version: 2.0.5

12 NC: 8670 000 60173
EAN: 87 12581 52642 9

© 2012 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com