

Philips  
Ear clip headphones



SHS4700



## Clip-on comfort

### Clip on comfort

Give your ears the most comfortable fit ever. These fully adjustable headphones with their ultra-soft ear cushions adapt to your head for an extra secure and comfortable fit, ensuring hours of enjoyable listening.

#### For superb music pleasure

- Bass beat vents allow air movement for better sound
- Neodymium magnet enhances bass performance and sensitivity
- 24 k gold-plated plug ensures an ultra-reliable connection

#### Made to fit you

- Super-soft ear cushions for hours of comfort
- Flexible rubber ear hooks for a comfortable and secure fit
- Adjustable hinge and ear hook for added security and comfort

#### Always ready to go

- Tangle-free cable simplifies use and storage
- Asymmetric cable keeps the cable out the way
- Strain relief enhances cable and connection reliability
- A 1.2 m long cable that is ideal for outdoor use

# PHILIPS

# Specifications

## Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 12–24,000 Hz
- Impedance: 24 ohm
- Maximum power input: 100 mW
- Sensitivity: 115 dB
- Speaker diameter: 32 mm
- Type: Dynamic

## Connectivity

- Cable Connection: two-parallel, asymmetric
- Cable length: 1.2 m + 1.8 m
- Connector: 3.5 mm
- Finishing of connector: Gold-plated
- Type of cable: OFC

## Inner Carton

- Gross weight: 0.617 kg
- Inner carton (L x W x H): 23.3 x 18.5 x 11.3 cm

- Net weight: 0.459 kg
- Tare weight: 0.158 kg
- EAN: 87 10895 92145 9
- Number of consumer packages: 6

## Outer Carton

- Gross weight: 10.82 kg
- Outer carton (L x W x H): 47.5 x 40 x 48 cm
- Net weight: 3.264 kg
- Tare weight: 7.556 kg
- EAN: 87 10895 92146 6
- Number of consumer packages: 96

## Packaging dimensions

- Packaging dimensions (W x H x D): 10 x 22 x 2.8 cm
- Gross weight: 0.077 kg
- Net weight: 0.034 kg
- Tare weight: 0.043 kg
- EAN: 87 10895 92144 2
- Number of products included: 1
- Packaging type: Blister

# Highlights

## Bass Beat vents

Bass beat vents allow air movement for better sound with a deep, rich bass.

## Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

## 24 k Gold-plated plug

You can rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

## Super-soft ear cushions

The ear cushions are very soft and enclose the speakers around the ears to create great sound. With very little pressure on the ears, you can use the headphones comfortably for long periods.

## Flexible rubber ear hooks

The rubber ear hooks provide a non-slip grip for an extra secure and comfortable fit, ensuring that the headphones remain in place for hours of comfort. Ideal for active use.

## Fully adjustable

The adjustable hinge and ear hook give added security and comfort by adapting to the shape and size of your ear. This helps to give a perfect fit that is extremely comfortable and also keeps the headphones in place.

## Tangle-free cable

The tangle-free cable helps you save time, as it is less likely to become tangled. This is because it is made from a material that is more rigid yet maintains its flexibility.

## Asymmetric cabling system

This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.

## Strain relief

A soft, flexible sleeve protects the cable connection from damage that would otherwise occur from repeated bending, extending the product life.

## 1.2 m cable

The ideal cable length to give you the freedom to put your audio device where you want.



Issue date 2019-04-24

Version: 6.0.6

12 NC: 9082 100 05696  
EAN: 87 10895 92144 2

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)