



Philips
Earhook Headphones



SHS4800



Adjustable fit

Flexible earhook fits all ears

This inner earhook sleeves of this headphone can be adjusted to sit on 5 different positions for a more personalized fit. Air in-between the caps and speakers allows for a soft feel as the caps become softer like a cushion.

Music to your ears

- 24k gold-plated plug ensures an ultra reliable connection
- Bass beat vents allow air movement for better sound

Made to fit you and your lifestyle

- Contoured earhook increase wearing comfort and stability
- 13.5mm speaker driver optimizes wearing comfort
- Air cushioned caps for superb cushioning comfort

Always ready to go

- Stays comfortably in your ear when you are on the move
- Durable Flexi-Grip makes a strong flexible connection

PHILIPS

Specifications

Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Diaphragm: Mylar dome
- Voice coil: Copper
- Frequency response: 12 - 23 500 Hz
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 13.5mm
- Type: Dynamic

Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: Chrome plated
- Type of cable: OFC

Inner Carton

- Gross weight: 0.221 kg
- Inner carton (L x W x H): 10.7 x 10.4 x 19.1 cm

- Nett weight: 0.048 kg
- Tare weight: 0.173 kg
- EAN: 87 12581 50037 5
- Number of consumer packagings: 3

Outer Carton

- Gross weight: 2.186 kg
- Outer carton (L x W x H): 23.6 x 23 x 42.1 cm
- Nett weight: 0.384 kg
- Tare weight: 1.802 kg
- EAN: 87 12581 50038 2
- Number of consumer packagings: 24

Packaging dimensions

- Packaging dimensions (W x H x D): 9.5 x 17 x 3 cm
- Gross weight: 0.051 kg
- Nett weight: 0.016 kg
- Tare weight: 0.035 kg
- EAN: 87 12581 50036 8
- Number of products included: 1
- Packaging type: Blister

Highlights

Contoured earhook

The earhook stays put behind your ear even when you're on the move, keeping the earphone comfortably in place and sounding great. It's the part contacting the back of your ears and keeps the headphones on your ears.

Designed for active use

Whether you are out running, cycling or taking part in any active pastime, this headphone will stay comfortably in your ear.

13.5mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver undistorted sound, an ideal size for listening enjoyment.

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.


Air cushioned caps

Air in between the cap and the driver gives you a soft feel like a pillow as it reduces the pressure on your ears.

Bass beat vents

Bass beat vents allow air movement for better sound with a deep rich bass.

Flexi-grip design



The soft flexi-grip material that the body of the headphone is sheathed in enhances its performance and extends its durability. It protects the cable connection from damage that otherwise could occur due to repeated bending of the headphone body from frequent contact with the user's fingertips when being put on and removed.



Issue date 2014-02-23

Version: 4.0.6

12 NC: 8670 000 55629
EAN: 87 12581 50036 8

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com