

Philips
Earhook Headphones



SHS4840



Extra comfortable

Adjustable earhook fits all ears

This inner earhook sleeves of this headphone can be adjusted to sit on 5 different positions for a more personalized fit. Air in-between the caps and speakers allows for a soft feel as the caps become softer like a cushion.

Music to your ears

- Enjoy best-in-class performance and optimum sound quality
- Bass beat vents allow air movement for better sound

Made to fit you and your lifestyle

- Contoured earhook increase wearing comfort and stability
- 13.5mm speaker driver optimizes wearing comfort
- Air cushioned caps for superb cushioning comfort

Always ready to go

- Stays comfortably in your ear when you are on the move
- Durable Flexi-Grip makes a strong flexible connection

PHILIPS

Specifications

Packaging dimensions

- Packaging dimensions (W x H x D): 5.3 x 17.3 x 3.8 cm
- Packaging dimensions (W x H x D): 2.1 x 6.8 x 1.5 inch
- Nett weight: 0.0151 kg
- Nett weight: 0.033 lb
- Gross weight: 0.0356 kg
- Gross weight: 0.078 lb
- Tare weight: 0.0205 kg
- Tare weight: 0.045 lb
- UPC: 6 09585 18003 1
- Number of products included: 1
- Packaging type: Blister
- Type of shelf placement: Both

Outer Carton

- Outer carton (L x W x H): 36.8 x 21.4 x 14 cm
- Outer carton (L x W x H): 14.5 x 8.4 x 5.5 inch
- Nett weight: 0.3624 kg
- Nett weight: 0.799 lb
- Gross weight: 1.2944 kg
- Gross weight: 2.854 lb
- Tare weight: 0.932 kg
- Tare weight: 2.055 lb
- GTIN: 1 06 09585 18003 8
- Number of consumer packagings: 24

Inner Carton

- Inner carton (L x W x H): 20.6 x 17.9 x 6.3 cm

- Inner carton (L x W x H): 8.1 x 7.0 x 2.5 inch
- Nett weight: 0.0906 kg
- Nett weight: 0.200 lb
- Gross weight: 0.2886 kg
- Gross weight: 0.636 lb
- Tare weight: 0.198 kg
- Tare weight: 0.437 lb
- GTIN: 2 06 09585 18003 5
- Number of consumer packagings: 6

Sound

- Acoustic system: open
- Magnet type: Neodymium
- Diaphragm: Mylar dome
- Voice coil: copper
- Frequency response: 12 - 23 500 Hz
- Impedance: 16 ohm
- Sensitivity: 105 dB
- Speaker diameter: 13.5 mm
- Type: Dynamic
- Maximum power input: 15 mW

Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: chrome-plated
- Type of cable: OFC

Highlights

Contoured earhook

The earhook stays put behind your ear even when you're on the move, keeping the earphone comfortably in place and sounding great. It's the part contacting the back of your ears and keeps the headphones on your ears.

Designed for active use

Whether you are out running, cycling or taking part in any active pastime, this headphone will stay comfortably in your ear.

13.5mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver undistorted sound, an ideal size for listening enjoyment.

Air cushioned caps

Air in between the cap and the driver gives you a soft feel like a pillow as it reduces the pressure on your ears.

Bass beat vents

Bass beat vents allow air movement for better sound with a deep rich bass.

Flexi-grip design

The soft flexi-grip material that the body of the headphone is sheathed in enhances its performance and extends its durability. It protects the cable connection from damage that otherwise could occur due to repeated bending of the headphone body from frequent contact with the user's fingertips when being put on and removed.



Issue date 2017-05-09

Version: 4.1.12

12 NC: 8670 000 57986
UPC: 6 09585 18003 1

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com