

Philips
Neckband Headphones



SHS8200



Extra Bass

Ultra compact folds flat for storage

The large 32 mm speaker drivers and bass beat vents create a spectacular big bass beat sound, while the ultra-flat foldable neckband is easy to store and carry.

Music to your ears

- 32 mm speaker driver delivers high-performance sound
- Bass beat vents allow air movement for better sound
- Neodymium magnet enhances bass performance and sensitivity
- Enjoy best-in-class performance and optimum sound quality
- 24 k gold-plated plug ensures an ultra-reliable connection

Made to fit you and your lifestyle

- Ultra-soft fabric for maximum wearing comfort
- Contoured design around the neck, for comfortable fit
- Ergonomically shaped headphone enhances user comfort

Always ready to go

- Flat when folded, it fits easily in your travel bag
- Reinforced cable connection ensures extra durability
- Single-sided cable reduces tangling and improves comfort
- A 1.2 m long cable that is ideal for outdoor use

PHILIPS
sense and simplicity

Specifications

Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 12–24,000 Hz
- Impedance: 24 ohm
- Maximum power input: 100 mW
- Sensitivity: 106 dB
- Speaker diameter: 32 mm
- Type: Dynamic

Connectivity

- Cable Connection: one-sided
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: Gold-plated
- Type of cable: OFC

Packaging dimensions

- Packaging dimensions (W x H x D): 12.5 x 23.2 x 3.2 cm

- Net weight: 0.056 kg
- Gross weight: 0.14 kg
- Tare weight: 0.084 kg
- EAN: 87 10895 93689 7
- Number of products included: 1
- Packaging type: Blister

Outer Carton

- Outer carton (L x W x H): 51 x 30 x 56 cm
- Net weight: 8.72 kg
- Gross weight: 9.4 kg
- Tare weight: 0.68 kg
- EAN: 87 10895 93691 0
- Number of consumer packages: 48

Inner Carton

- Inner carton (L x W x H): 24 x 13.5 x 26 cm
- Net weight: 0.84 kg
- Gross weight: 1.09 kg
- Tare weight: 0.25 kg
- EAN: 87 10895 93690 3
- Number of consumer packages: 6

Highlights

32 mm speaker driver

The 32 mm speaker driver is a compact yet powerful element for delivering non-distorted sound with any given input power.

Bass Beat vents

Bass beat vents allow air movement for better sound with a deep, rich bass.

Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

Excellent sound quality

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance.

24 k Gold-plated plug

You can rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

Ultra-soft fabric

The ultra-soft material used is soft on the skin, for maximum wearing comfort.

Contoured design

Contoured design around the neck, for comfortable fit

Comfort fit

This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.

Real Flat folding

The headphone set is designed to be folded flat, so that it fits in your travel bag easily.

Reinforced cable connection

A soft plastic part on the ear shell reduces cable strain, protects the connection and prevents damage from repeated bending.

Single-sided cable

The cable is conveniently connected to just one side, considerably reducing the risk of tangling and simplifying winding the cable up for storage.

1.2 m cable

The ideal cable length to give you the freedom to put your audio device where you want.



Issue date 2010-12-10

Version: 3.0.7

12 NC: 9082 100 06523
EAN: 87 10895 93689 7

© 2010 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com