

Philips  
Neckband Headphones

SHS850



## Extra Comfort !

Fabric-covered neckband headphone

Here's evidence that style, comfort and performance go hand in hand. The fabric-covered SHS850 neckband headphone brings a totally new look to personal music enjoyment, and features incredibly soft ear hooks that you'll hardly even feel.

### Music to your ears

- 32mm speaker driver delivers high performance sound
- 24k gold-plated plug ensures an ultra reliable connection
- Copper Cladded Aluminium Wire improves sound quality
- Neodymium magnet enhances bass performance and sensitivity

### Made to fit you and your lifestyle

- Ear cushions improve wearing comfort and bass response
- Lightweight design improves comfort for prolonged use.
- A special soft touch rubber material covers the ear hook.

### Always ready to go

- Headphone neckband folds up for convenient storage
- Rear cable exit enhances comfort and convenience

**PHILIPS**  
sense and simplicity

## Specifications

### Sound

- **Acoustic system:** Open
- **Magnet type:** Neodymium
- **Diaphragm:** Mylar dome
- **Voice coil:** CCAW
- **Frequency response:** 10 - 24 000 Hz
- **Impedance:** 24 Ohm
- **Maximum power input:** 100 mW
- **Sensitivity:** 106 dB
- **Speaker diameter:** 32 mm
- **Type:** Dynamic

### Connectivity

- **Cable Connection:** One-sided
- **Cable length:** 1.2 m
- **Connector:** 3.5 mm stereo
- **Finishing of connector:** 24k Gold-plated
- **Type of cable:** OFC

### Inner Carton

- **EAN:** 87 10895 87978 1
- **Gross weight:** 0.752 kg

- **Inner carton (L x W x H):** 39 x 19 x 25.5 cm
- **Nett weight:** 0.352 kg
- **Number of consumer packagings:** 6
- **Tare weight:** 0.4 kg

### Outer Carton

- **EAN:** 87 10895 87979 8
- **Gross weight:** 7.63 kg
- **Outer carton (L x W x H):** 81 x 41 x 54 cm
- **Nett weight:** 2.813 kg
- **Number of consumer packagings:** 48
- **Tare weight:** 4.817 kg

### Packaging dimensions

- **Packaging dimensions (W x H x D):** 17.5 x 23.6 x 6.5 cm
- **EAN:** 87 10895 87977 4
- **Gross weight:** 0.125 kg
- **Nett weight:** 0.059 kg
- **Number of products included:** 1
- **Packaging type:** Blister
- **Tare weight:** 0.066 kg

## Product highlights

### 32 mm speaker driver

The 32 mm speaker driver is a compact yet powerful element for delivering non-distorted sound with any given input power.

### 24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

### CCA W voice coil

By using top-quality Copper Cladded Aluminium Wire (CCA W) in the headphone driver's voice coil, the sound quality is considerably improved.

### Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

### Comfort ear cushions

The special shape and luxurious materials used for the ear cushions ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

### Lightweight design

The durable, lightweight quality materials enhance comfort for extended wearing.

### Rubberised ear hook

The special soft touch rubber that covers the ear hook is both comfortable and secure.

### Foldable neckband

The headphone can fold down to a small size for convenient storage when not in use.

### Rear cable exit

The headphone cable is centred at the back of the neckband so you're hardly aware it's even there.



Issue date 2007-10-22

Version: 3.0

12 NC: 9082 100 04317  
EAN: 87 10895 87977 4

© 2007 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)