

Saeco PicoBaristo  
Super-automatic  
espresso machine

- 11 Beverages
- Integrated premium milk carafe
- Silver
- AquaClean



SM3061/10

The largest variety from a compact machine

Enjoy up to 5000 cups\* of coffee without descaling

PicoBaristo is a compact machine which spoils coffee lovers for variety. Via the user interface you can choose from a wide choice of specialties at one touch. And with the AquaClean filter you can enjoy up to 5,000 cups\* without descaling

**Any coffee for any moment**

- Enjoy 11 beverages at your fingertips
- One-touch Cappuccino and Latte Macchiato with milk carafe
- Adjust the length, 5 aroma strength and 10 grinder settings
- Adjust and store your personal user profile

**Every coffee crafted to perfection**

- 20,000 cups of finest coffee with durable ceramic grinders
- Perfect milk foam thanks to Latte Perfetto technology
- Hot coffee from the first cup with Thermoblock
- Premium Silver finishing, shaped to precision

**Attentive and anticipating at your command**

- Featuring AquaClean for up to 5000\* cups without descaling
- Clean milk residues after every use with milk clean function
- Enhanced control of your machine via the advanced display
- Designed to maximize capacities in a compact footprint

 **Saeco**

**PHILIPS**

Saeco, a Philips brand



# Highlights

## 100% ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

## 11 beverages

Enjoy a wide variety of drinks to suit any occasion. Whether you crave for an espresso, a coffee or a milk based recipe, your Super-automatic machine delivers a perfect in-cup result with no hassle and in no time!

## Advanced Display



The advanced display shows you all relevant information to easily interact with your machine and get the best performance. The

combination of icons and text will guide you through all customisation options and important maintenance activities.

## AquaClean filter



# AquaClean

AquaClean is our patented water filter, designed to improve the quality of your coffee by purifying water. It also prevents scale build-up in the water circuit of your coffee machine: make up to 5000\* cups without descaling by replacing the filter regularly.

## Auto-Rinse & Guided descaling



This espresso machine automatically cleans its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will


prompt when descaling is needed. It will guide you with on-screen messages what you have to do and when.

## Customize your coffees



This Super-Automatic machine offers an abundance of indulgent options to customize your beverage to your taste. You can easily personalize and memorize length, strength and temperature for each drink. Feel free to explore, experiment and dream up any drink!

## High capacity & compact design



Enjoy more room and go longer without refill thanks to the high-capacity bean, water, and waste containers in a super-compact design. This smart, super-automatic machine provides you with maximum convenience and top notch performance thanks to a large capacity water tank, bean and waste container.

# Specifications

## General specifications

- Type of carafe: Premium carafe
- Milk Solution: Integrated Milk Carafe
- User Interface: Advanced display

## Technical specifications

- Capacity milk carafe: 0.5 L
- Capacity waste container: 15 servings
- Capacity water tank: 1.8 L
- Frequency: 50 Hz
- Max. cup height: 163 mm
- Voltage: 230 V
- Coffee bean capacity: 250 g
- Color & Finishing: Silver Paint
- Cord length: >100 cm
- Filter compatibility: AquaClean
- Product dimensions: 221 x 340 x 430 mm
- Waste container: Frontal access
- Water tank: Access from the top
- Country of origin: Romania

## Customization

- Aroma Strength Settings: 5

- Coffee and Milk Length: Adjustable
- Grinder Settings: 10
- Pre Brew Aroma control: No
- Temperature settings: 3
- User Profiles: 1

## Other features

- Auto-Rinse & Guided descaling
- Gusto perfetto
- Main Switch ON / OFF button
- Quick Heat Boiler
- Removable brew group

## Variety

- Beverages: Baby Cappuccino, Caffè crema, Cappuccino, Espresso, Espresso Double, Espresso Lungo, Flat White, Hot water, Latte Macchiato, Milk froth, Ristretto
- Coffee Powder Option
- Double Cup
- Milk Double Cup: No