



**Saeco Xelsis  
Super-automatic  
espresso machine**

- 15 Beverages
- Latteduo system
- Titanium Front
- 12-step adjustable grinder



**SM7684/00**

Exquisite coffee, easily crafted to your taste

Craft 15 drinks at a touch with Coffee Equalizer™

From strong ristretto to perfect cappuccino - create coffee experiences that satisfy your demands. Simply swipe the touchscreen to choose from 15 recipes. Coffee Equalizer™ fine tunes coffee recipes for discerning coffee drinkers.

**Barista coffees at your command**

- 15 of the world's best coffee drinks at your fingertips
- Our most advanced touch screen display
- Makes 2 cups of coffee drinks at once, including Cappuccino
- 6 user profiles: the easiest way to store your recipes

**Superior taste, time after time**

- 20,000 cups of finest coffee with durable ceramic grinders
- Saeco extracts the best part of your fresh coffee beans
- Excellent milk foam thanks to our Latte Perfetto technology
- High-performance quick heating water Thermoblock

**Effortless cleaning and maintenance**

- Featuring AquaClean for up to 5000\* cups without descaling
- Proven hygiene of milk system with steam cleaning
- Internal brew group is easy to remove and rinses in seconds
- Three-click cleaning and maintenance system

**PHILIPS**

Saeco, a Philips brand

 **Saeco**



# Highlights

## 15 different coffee drinks



Enjoy unlimited variety, from espresso and cappuccino specialty coffee drinks like Americanos and Flat Whites. So you can serve everyone the drink they prefer.

## Touchscreen Coffee Equalizer™



Intuitively adjust the characteristics of your drinks via the touch screen thanks to the Coffee Equalizer™: you can customise the strength, volume, temperature and taste of coffee, the milk foam amount and volume, and even the coffee and milk order. Craft your coffee the way you prefer.

## 100% ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

## AquaClean filter



## AquaClean

AquaClean is our patented water filter, designed to improve the quality of your coffee by purifying water. It also prevents scale build-up in the water circuit of your coffee machine: make up to 5000\* cups without descaling by replacing the filter regularly.

## Automatic milk system cleaning



The HygieSteam function will clean up the whole milk circuit with steam, from the spout to the milk tubes, at your command. In addition, each time you make a drink with milk, Saeco Xelsis automatically cleans the milk system with a jet of hygienic steam, so it is clean and ready to make your next drink.

## LatteDuo function



Create your favorite coffee drinks, including Cappuccinos and Latte macchiatos in single or double servings, all with just one touch.

## Fully removable brewing group



The internal brewing group is easy to remove, and rinses clean in seconds. So the core of your Saeco Xelsis is always ready to make superior coffee.

## Easy cleaning and maintenance



With just three clicks, Saeco Xelsis starts the cleaning process it needs to keep on making excellent coffees and beverages for you.



### IF Design Award

The iF DESIGN AWARD is among the most prestigious and largest design competitions in the world

Saeco won an iF Design award 2018: since 1953, a seal of excellence, a testimony of quality and a symbol of trust for users. This prestigious prize is awarded every year by iF International Forum Design GmbH in Hannover (Germany), the world's oldest independent design organization.

# Specifications

## Accessories

- Included: Measuring scoop, Water hardness test strip, Cleaning brush, Brew group grease, Milk container, AquaClean filter

## Finishing

- Material of main body: Stainless steel / ABS

## General specifications

- Customizing per drink: Adjustable milk foam amount, Adjustable coffee strength, Adjustable cup volume, Adjustable temperature, User profiles, Adjustable milk/coffee order, Adjustable coffee taste
- Grinder settings: 12
- Number of user profiles: 8
- Type of boiler: Stainless steel boiler
- Type of carafe: Milk container
- Type of display: TFT
- Adjustable spout height: 75-148 mm
- Milk Solution: Latte Perfetto technology
- User Interface: Touch screen display
- Special functions: Ground coffee option

## Service

- 2-year worldwide guarantee

## Sustainability

- Energy label: A-class
- Power consumption stand-by: <0.5 W

## Technical specifications

- Capacity milk carafe: 0.6 L

- Capacity waste container: 14 servings
- Capacity water tank: 1.7 L
- Coffee bean capacity: 450 g
- Filter compatibility: AquaClean
- Waste container: Frontal access
- Water tank: Frontal access
- Country of origin: Italy
- Drip tray capacity: 500 ml

## Weight and dimensions

- Dimensions of product (WxDxH): 283x489x393 mm

## Customization

- Aroma Strength Settings: 5
- Coffee and Milk Length: Adjustable
- Grinder Settings: 12
- Pre Brew Aroma control
- Temperature settings: 3
- User Profiles: 6

## Other features

- Auto-Rinse & Guided descaling
- Main Switch ON / OFF button
- Quick Heat Boiler
- Removable brew group
- LED illuminated water tank
- Warm milk function

## Design

- Color: Black, Titanium