

Philips Momentum
Wired gaming mouse

3 buttons

USB Wired
Optical Sensor
7-way ambiglow lighting



SPK9314



Get in the moment

Fast, accurate, and exciting, all you need for gaming. The split design G314 gaming mouse, with very high accuracy will help you edge out the competition.

Advanced technology for ultimate performance

- Up to 6,000 FPS refresh rate for quick action
- Return rate (Polling rate): 500Hz

Advanced customization for performance

- Looks to match your rig with 7-way lighting effects

Durable and lightweight

- Braided cord for a longer lasting upgraded look
- Up-to 5 Million click lifespan

PHILIPS

Wired gaming mouse
3 buttons USB Wired, Optical Sensor, 7-way ambiglow lighting

Specifications

Technical specifications

- Product Type: High performance gaming mouse
- Design Type: Ergonomic design
- Connectivity: USB 2.0 wired
- Buttons: 3 buttons
- Optical Sensor Precision: 1200 DPI
- Frames Per Second: 6000 FPS
- Polling Rate: 500Hz
- Driver Requirement: Driver-free
- Lighting Effect Type: 7-way lighting

- Coating Type: Matte UV coating
- Key Lifespan: 5 Million

Physical Dimensions

- Dimensions (LxWxH): 118.5*64*37mm
- Weight: 110g

OS/System Requirements

- System Requirements: Microsoft Windows XP, Windows Vista, Windows 7, Windows 8, Windows 11 or later; Linux; Mac OS

SPK9314/94

Highlights

Braided cord

Braided cord for a longer lasting upgraded look

Return rate 500Hz



Return rate (Polling rate): 500Hz

Up to 6,000 FPS refresh rate




Up to 6,000 FPS refresh rate for quick action

Up-to 5 Million click lifespan



Up-to 5 Million click lifespan

7-way backlit effects



Looks to match your rig with 7-way lighting effects



Issue date 2021-12-09

Version: 1.0.1

12 NC: 8670 001 74133
EAN: 87 12581 77579 7

© 2021 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com