

Philips
LCD wall mount

Full motion

SQM4512



Full motion wall mount

LCD

Designed to fit most brands of TV with a focus on safety & ease of use. Easy 1-2-3 installation kit includes necessary hardware for different wall types, templates, stud finder, bubble level. UL certified for weight capacity up to 40 lbs.

Maximizes viewing angles

- Full motion arm
- + / - 15° tilt
- 180° swivel

Fits most TV brands

- UL/CUL approved for weight capacity
- Screen sizes 43 - 81 cm (17" - 32")
- VESA 75,100,100x200,200

Easy installation

- Mounting templates
- Mounting hardware
- Bubble level and stud finder

PHILIPS

LCD wall mount
Full motion

Specifications

Packaging dimensions

- Packaging dimensions (W x H x D):
26.1 x 25.5 x 5.8 cm
- Packaging dimensions (W x H x D):
10.3 x 10.0 x 2.3 inch
- Gross weight: 1.54 kg
- Gross weight: 3.395 lb
- Nett weight: 2.910 lb
- Nett weight: 1.32 kg
- Tare weight: 0.485 lb
- Tare weight: 0.22 kg
- Number of products included: 1
- Packaging type: Carton
- UPC: 6 09585 14903 8

Outer Carton

- Outer carton (L x W x H): 52 x 27.2 x 12.4 cm
- Outer carton (L x W x H): 20.5 x 10.7 x 4.9 inch
- Gross weight: 14.771 lb
- Gross weight: 6.7 kg
- Nett weight: 5.28 kg
- Nett weight: 11.640 lb
- Tare weight: 1.42 kg
- Tare weight: 3.131 lb
- GTIN: 1 06 09585 14903 5
- Number of consumer packagings: 4

SQM4512/27

Highlights

Full motion arm

Extends the TV out from the wall, providing a +/-15° tilt and 180° swivel to maximize viewing angles.

+ / - 15° tilt

Allow the TV to be adjusted up and down + / - 15° to attain the optimum viewing angle.

180° swivel

Allow the TV to adjust left and right 180° to attain the optimum viewing angle.

UL/CUL weight approved

Compliance with Underwriters Laboratories requirements for weight certification ensures the wall mount will safely hold your TV.

Mounting templates

Paper guides indicate the ideal hole pattern for drilling into walls, ensuring users of exactly the right hole configuration.

Mounting hardware

Includes all necessary screws, anchors and bolts for different types of walls, ensuring the right type of hardware is readily available for the particular type of wall the support is being mounted on.

Bubble level and stud finder

Includes both tools necessary for installation. A bubble level ensures a straight line. A stud finder quickly, easily and accurately locates studs in the wall.

VESA 75,100,100x200,200

Compliance with the Video Electronics Standards Association requirements for bolt patterns ensures that the wall support matches up to the bolt pattern on your specific TV.



Issue date 2014-03-14

Version: 5.0.7

12 NC: 8670 000 37244
UPC: 6 09585 14903 8

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com