

Philips SafeRide  
LED BikeLightbattery  
driven



SRFB40BLX



# Take control over your safety

Feel Safe, Ride Safe

## Extra wide illumination

- Foreground illumination
- Glare free beam
- High efficiency reflector

## Easy installation, easy integration

- Can be mounted on all types of bikes
- Compact design

## Maximum light output

- 70 lumen in the beam
- Crystal white light (5500 K)
- Length of beam: 30 metres
- Powered by High-Power LUXEON LED

**PHILIPS**  
sense and simplicity

# Specifications

## Ease of use

- Application: Day, Night
- Easy installation

- Long life LED technology
- USB charger: Yes, UK compatible
- Waterproof aluminium housing

# Highlights

## Foreground illumination

Foreground illumination

## Glare free beam

Glare free beam

## High efficiency reflector

High efficiency reflector

## Can be mounted on all bikes

Can be mounted on all types of bikes

## Compact design

Compact design

## 70 lumen in the beam

70 lumen in the beam

## Crystal white light (5500 K)

Crystal white light (5500 K)

## Length of beam: 30 metres

Length of beam: 30 metres

## Powered by High-Power LUXEON

Powered by High-Power LUXEON LED



Issue date 2013-01-10

Version: 1.0.1

12 NC: 9282 216 10102  
EAN: 87 27900 35275 7

© 2013 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)