

Philips  
3.5mm - composite AV  
cable

9 ft

SWA3163W



## Ensure a reliable connection

with this Stereo Y cable

Experience a new level of listening while transferring audio signals between your components. Superior construction delivers improved sound performance.

### Enjoy better audio quality

- 24 carat gold-plated connectors optimize signal
- High purity copper conductor for reliable signal transfer

### Protects against signal loss

- Copper braided reinforced aluminum shielding

### Easy installation

- Color coded connectors for instant recognition
- Non-slip ergonomic grip for easy use
- Plug and play for easy use

### Enjoy extended durability

- Protective metal shell for extended durability
- Flexible PVC jacket
- Rubber strain relief

**PHILIPS**  
sense and simplicity

3.5mm - composite AV cable  
9 ft

# Specifications

## Inner Carton

- GTIN: 1 06 09585 15115 1
- Number of consumer packagings: 2
- Inner carton (L x W x H): 27.5 x 10.2 x 10.5 cm
- Gross weight: 0.485 kg
- Nett weight: 0.276 kg
- Tare weight: 0.209 kg

## Outer Carton

- GTIN: 2 06 09585 15115 8
- Number of consumer packagings: 4
- Outer carton (L x W x H): 28 x 22.5 x 11.5 cm
- Gross weight: 0.975 kg

- Nett weight: 0.552 kg
- Tare weight: 0.423 kg

## Packaging dimensions

- UPC: 6 09585 15115 4
- Number of products included: 1
- Packaging type: Blister
- Packaging dimensions (W x H x D): 9.4 x 26.4 x 4.7 cm
- Gross weight: 0.22 kg
- Nett weight: 0.138 kg
- Tare weight: 0.082 kg

SWA3163W/17

# Highlights

## Color-coded connectors

Color coded connections make it easy to install your cable into the correct inputs and outputs

## Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

## 24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

## Braided shielding

Copper braided reinforced aluminum shielding protects against signal loss and interference.

## Metal shell

The metal shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

## Flexible PVC Jacket

Flexible PVC jacket provided protection to the delicate core of the cable. It also offers extended durability and ease of installation.

## High purity copper

This copper conductor provides high accuracy in signal transfer with minimal resistance.

## Plug and play

Plug and play offers easy installation of components without time-consuming installations.

## Rubber strain relief

Rubber strain relief provides a secure, yet flexible juncture between the cable and the plug.



Issue date 2010-05-20

Version: 1.0.10

12 NC: 8670 000 37925  
UPC: 6 09585 15115 4

© 2010 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)