

Philips
Digital coax cable

1,5 m

SWA6305



Enjoy the ultimate listening experience

with this digital coax cable

Take your components to optimum performance. This top of the line cable offers the best connection for transferring audio signals between components.

Enjoy better audio quality

- High quality digital cable for great signal transfer
- 24 carat gold-plated connectors optimize signal
- 4-Cut connectors for secure connections

Protects against signal loss

- 100% aluminum shielding
- Oxygen-free copper conductor for ideal signal transfer
- Copper braided shielding

Easy installation

- Color coded connectors for instant recognition
- Non-slip ergonomic grip for easy use
- Plug and play for easy use

Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility

PHILIPS

Digital coax cable
1,5 m

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 94903 3
- Gross weight: .24 kg
- Tare weight: .01 kg
- Net weight: .23 kg
- Length: 222 mm
- Width: 159 mm
- Height: 64 mm

Inner Carton

- Gross weight: 0.75 kg
- Tare weight: 0.13 kg

Outer Carton

- EAN/UPC/GTIN: 87 10895 95243 9
- Quantity: 4
- Gross weight: .93 kg
- Tare weight: .01 kg
- Net weight: .92 kg
- Length: 234 mm
- Width: 211 mm
- Height: 176 mm

SWA6305/10

Highlights

Digital signal transfer

High quality cable provides great signal transfer, using digital technology.

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

4-Cut connectors

4-Cut connectors ensure secure connections between your component and your cable.

100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

Twisted high purity OFC

This oxygen-free copper conductor provides the highest accuracy in signal transfer with minimal resistance.

Copper braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

Color-coded connectors

Color coded connections make it easy to install your cable into the correct inputs and outputs

Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.



Issue date 2019-04-24

Version: 3.0.9

12 NC: 9082 100 07329
EAN: 87 10895 94903 3

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com