

Philips
Digital coax cable

1.5 m

SWA6305



Enjoy the ultimate listening experience

with this digital coax cable

Take your components to optimum performance. This top-of-the-line cable offers the best connection for transferring audio signals between components.

Enjoy better audio quality

- High-quality digital cable for great signal transfer
- 24 carat gold-plated connectors optimise signal
- 4-Cut connectors for secure connections

Protects against signal loss

- 100% aluminium shielding
- Oxygen-free copper conductor for ideal signal transfer
- Copper-braided shielding

Easy installation

- Colour-coded connectors for instant recognition
- Non-slip ergonomic grip for easy use
- Plug and play for easy use

Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility

PHILIPS
sense and simplicity

Digital coax cable
1.5 m

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 94903 3
- Gross weight: .24 kg
- Tare weight: .01 kg
- Net weight: .23 kg
- Length: 222 mm
- Width: 159 mm
- Height: 64 mm

Inner Box

- Gross weight: 0.75 kg
- Tare weight: 0.13 kg

Outer Box

- EAN/UPC/GTIN: 87 10895 95243 9
- Quantity: 4
- Gross weight: .93 kg
- Tare weight: .01 kg
- Net weight: .92 kg
- Length: 234 mm
- Width: 211 mm
- Height: 176 mm

SWA6305/10

Highlights

Digital signal transfer

High-quality cable provides great signal transfer, using digital technology.

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

4-Cut connectors

4-Cut connectors ensure secure connections between your component and your cable.

100% aluminium shielding

This protective layer of aluminium guards against electromagnetic interference for improved signal quality.

Twisted high-purity OFC

This oxygen-free copper conductor provides the highest accuracy in signal transfer with minimal resistance.

Copper-braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

Colour-coded connectors

Colour-coded connections make it easy to install your cable into the correct inputs and outputs

Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.



Issue date 2009-05-31

Version: 3.0.9

12 NC: 9082 100 07329
EAN: 87 10895 94903 3

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com