

Philips
Stereo audio cable

1,5 m

SWA6310



Enjoy the ultimate listening experience

with this stereo audio cable

Take your components to optimum performance. This top of the line cable offers the best connection for transferring video signals between components.

Enjoy better audio quality

- 99.97% Oxygen-Free Copper (OFC)
- 24 carat gold-plated connectors optimize signal
- 4-Cut connectors for secure connections
- Split center pin for better signal transfer

Protects against signal loss

- 100% aluminum shielding
- Oxygen-free copper conductor for ideal signal transfer
- Copper braided shielding
- Foam Polyethylene (FPE) Dielectric

Easy installation

- Color coded cable for easy polarity identification
- Plug and play for easy use

Enjoy extended durability

- Super pliable jackets for outstanding flexibility

PHILIPS

Stereo audio cable
1,5 m

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 93139 7
- Gross weight: .24 kg
- Tare weight: .01 kg
- Net weight: .23 kg
- Length: 273 mm
- Width: 197 mm
- Height: 89 mm

Inner Carton

- Gross weight: 0.75 kg
- Tare weight: 0.13 kg

Outer Carton

- EAN/UPC/GTIN: 87 10895 94986 6
- Quantity: 4
- Gross weight: .93 kg
- Tare weight: .01 kg
- Net weight: .92 kg
- Length: 323 mm
- Width: 300 mm
- Height: 211 mm

SWA6310/10

Highlights

99.97% OFC solid conductor

99.97% Oxygen-free copper (OFC) cable core provides optimum signal quality.

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

4-Cut connectors

4-Cut connectors ensure secure connections between your component and your cable.

Split center pin

The split center pin allows for better signal transfer and an improved connection to the component inputs.

100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

Twisted high purity OFC

This oxygen-free copper conductor provides the highest accuracy in signal transfer with minimal resistance.

Copper braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

FPE Dielectric

Foam Polyethylene (FPE) dielectric is a superior insulation material that protects against signal loss.

Color coded cables

Tinned copper and bare copper conductors provide easy polarity identification.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.



Issue date 2019-04-24

Version: 2.1.8

12 NC: 9082 100 05992
EAN: 87 10895 93139 7

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com