

Philips
Stereo audio cable

3.0 m

SWA6311



Enjoy the ultimate listening experience

with this stereo audio cable

Take your components to optimum performance. This top of the line cable offers the best connection for transferring audio signals between components.

Enjoy better audio quality

- 24 carat gold-plated connectors optimize signal
- 4-Cut connectors for secure connections
- Split center pin for better signal transfer

Protects against signal loss

- 100% aluminum shielding
- Foam Polyethylene (FPE) Dielectric
- Copper braided shielding

Easy installation

- Color coded connectors for instant recognition
- Non-slip ergonomic grip for easy use
- Plug and play for easy use

Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility

PHILIPS

Stereo audio cable
3.0 m

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 95420 4
- Gross weight: .58 kg
- Tare weight: .13 kg
- Net weight: .45 kg
- Length: 285 mm
- Width: 200 mm
- Height: 90 mm

Inner Carton

- EAN/UPC/GTIN: 87 10895 97650 3
- Quantity: 2
- Gross weight: 1.5 kg
- Tare weight: .6 kg

- Net weight: .9 kg
- Length: 315 mm
- Width: 150 mm
- Height: 210 mm

Outer Carton

- EAN/UPC/GTIN: 87 10895 94651 0
- Quantity: 4
- Gross weight: 3.64 kg
- Tare weight: 1.84 kg
- Net weight: 1.8 kg
- Length: 330 mm
- Width: 325 mm
- Height: 235 mm

SWA6311/93

Highlights

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

4-Cut connectors

4-Cut connectors ensure secure connections between your component and your cable.

Split center pin

The split center pin allows for better signal transfer and an improved connection to the component inputs.

100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

FPE Dielectric

Foam Polyethylene (FPE) dielectric is a superior insulation material that protects against signal loss.

Copper braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

Color-coded connectors

Color coded connections make it easy to install your cable into the correct inputs and outputs

Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.



Issue date 2019-08-29

Version: 4.0.9

12 NC: 9082 100 07577
EAN: 69 51613 98772 8

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com