

Philips  
Fiber optic cable

1,5 m

SWA6360



## Enjoy the ultimate listening experience

with this fibre optic cable

Take your components to optimum performance. This top of the line speaker wire offers the best connection for transferring audio signals between components.

### Enjoy better audio quality

- High quality digital cable for great signal transfer

### Protects against signal loss

- 100% aluminum shielding
- Oxygen-free copper conductor for ideal signal transfer
- Copper braided shielding
- Foam Polyethylene (FPE) Dielectric

### Easy installation

- Color coded connectors for instant recognition
- Plug and play for easy use

### Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility
- Reliable metal strain relief

# PHILIPS

Fiber optic cable  
1,5 m

# Specifications

## Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 93143 4
- Gross weight: .24 kg
- Tare weight: .01 kg
- Net weight: .23 kg
- Length: 222 mm
- Width: 159 mm
- Height: 64 mm

## Outer Carton

- EAN/UPC/GTIN: 87 10895 94988 0
- Quantity: 4
- Gross weight: .93 kg
- Tare weight: .01 kg
- Net weight: .92 kg
- Length: 234 mm
- Width: 211 mm
- Height: 175 mm

SWA6360/10

# Highlights

## Digital signal transfer

High quality cable provides great signal transfer, using digital technology.

## 100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

## Twisted high purity OFC

This oxygen-free copper conductor provides the highest accuracy in signal transfer with minimal resistance.

## Copper braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

## FPE Dielectric

Foam Polyethylene (FPE) dielectric is a superior insulation material that protects against signal loss.

## Color-coded connectors

Color coded connections make it easy to install your cable into the correct inputs and outputs

## Plug and play

Plug and play offers easy installation of components without time-consuming installations.

## Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

## Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.

## Metal strain relief

Full metal connector ensures extended durability by preventing damage during use and installation.



Issue date 2014-02-06

Version: 2.1.6

12 NC: 9082 100 06002  
EAN: 87 10895 93143 4

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)