

Philips
Fibre optic cable

1.5 m

SWA6360



Enjoy the ultimate listening experience

with this fibre optic cable

Take your components to optimum performance. This top-of-the-line speaker wire offers the best connection for transferring audio signals between components.

Enjoy better audio quality

- High-quality digital cable for great signal transfer

Protects against signal loss

- 100% aluminium shielding
- Oxygen-free copper conductor for ideal signal transfer
- Copper-braided shielding
- Foam Polyethylene (FPE) Dielectric

Easy installation

- Colour-coded connectors for instant recognition
- Plug and play for easy use

Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility
- Reliable metal strain relief

PHILIPS
sense and simplicity

Fibre optic cable
1.5 m

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 93143 4
- Gross weight: .24 kg
- Tare weight: .01 kg
- Net weight: .23 kg
- Length: 222 mm
- Width: 159 mm
- Height: 64 mm

Outer Box

- EAN/UPC/GTIN: 87 10895 94988 0
- Quantity: 4
- Gross weight: .93 kg
- Tare weight: .01 kg
- Net weight: .92 kg
- Length: 234 mm
- Width: 211 mm
- Height: 175 mm

SWA6360/10

Highlights

Digital signal transfer

High-quality cable provides great signal transfer, using digital technology.

100% aluminium shielding

This protective layer of aluminium guards against electromagnetic interference for improved signal quality.

Twisted high-purity OFC

This oxygen-free copper conductor provides the highest accuracy in signal transfer with minimal resistance.

Copper-braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

FPE Dielectric

Foam Polyethylene (FPE) dielectric is a superior insulation material that protects against signal loss.

Colour-coded connectors

Colour-coded connections make it easy to install your cable into the correct inputs and outputs

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.

Metal strain relief

Full metal connector ensures extended durability by preventing damage during use and installation.



Issue date 2009-05-31

Version: 2.1.6

12 NC: 9082 100 06002
EAN: 87 10895 93143 4

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com