

Philips
Digital coax cable

5 m

SWA6724



Enjoy the ultimate listening experience

with this digital coax cable

Take your components to optimum performance. This top-of-the-range cable offers the best connection for transferring audio signals between components.

Enjoy better audio quality

- High-quality digital cable for great signal transfer
- Split centre pin for better signal transfer

Protects against signal loss

- 100% aluminium shielding
- Copper-braided shielding
- Foam Polyethylene (FPE) Dielectric

Easy installation

- Colour-coded connectors for instant recognition
- Non-slip ergonomic grip for easy use
- Plug and play for easy use

Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility
- Reliable metal strain relief

PHILIPS
sense and simplicity

Digital coax cable
5 m

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 99356 2
- Gross weight: 0.48 kg
- Tare weight: 0.01 kg
- Net weight: 47 kg
- Length: 285 mm
- Width: 200 mm
- Height: 90 mm

Inner Carton

- EAN/UPC/GTIN: 87 10895 99357 9
- Quantity: 2
- Gross weight: 1.18 kg
- Tare weight: 0.2 kg

- Net weight: 0.98 kg
- Length (cm): 31.5 cm
- Width (cm): 15 cm
- Height (cm): 21 cm

Outer Carton

- EAN/UPC/GTIN: 87 10895 99358 6
- Quantity: 4
- Gross weight: 3.08 kg
- Tare weight: 0.68 kg
- Net weight: 2.4 kg
- Length (cm): 23.5 cm
- Width (cm): 32.5 cm
- Height (cm): 33 cm

SWA6724/10

Highlights

Digital signal transfer

High-quality cable provides great signal transfer, using digital technology.

Split centre pin

The split centre pin allows for better signal transfer and an improved connection to the component inputs.

100% aluminium shielding

This protective layer of aluminium guards against electromagnetic interference for improved signal quality.

Copper-braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

FPE Dielectric

Foam Polyethylene (FPE) dielectric is a superior insulation material that protects against signal loss.

Colour-coded connectors

Colour-coded connections make it easy to install your cable into the correct inputs and outputs

Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.

Metal strain relief

Full metal connector ensures extended durability by preventing damage during use and installation.



Issue date 2009-08-05

Version: 1.0.6

12 NC: 9082 100 09731
EAN: 87 10895 99356 2

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com