

Philips  
HDMI cable

1.5 m  
High speed

SWV3534



## Supports resolutions up to 1080p

with this High-Speed HDMI™ cable

New High-Speed HDMI™ delivers the best digital audio and video performance possible with resolutions up to 1080p.

### **HDMI™ version 1.3a**

- Deep Color™
- Lossless Audio™

### **Enjoy better picture/sound quality**

- 24 carat gold-plated connectors optimise signal
- High-purity copper conductor for reliable signal transfer

### **Protects against signal loss**

- Copper-braided reinforced aluminium shielding

### **Easy installation**

- Non-slip ergonomic grip for easy use
- Plug and play for easy use

**PHILIPS**  
sense and simplicity

HDMI cable  
1.5 m High speed

# Specifications

## Packaging

- EAN/UPC/GTIN: 87 10895 93413 8
- Quantity: 1
- Gross weight: 0.160 kg
- Tare weight: 0.050 kg
- Net weight: 0.110 kg
- Length: 23.00 cm
- Width: 14.00 cm
- Height: 3.5 cm

## Inner Box

- EAN/UPC/GTIN: 87 10895 99670 9
- Quantity: 4
- Gross weight: 0.850 kg
- Tare weight: 0.210 kg
- Net weight: 0.640 kg
- Length (cm): 23.20 cm
- Width (cm): 14.20 cm
- Height (cm): 14.20 cm

## Outer Box

- EAN/UPC/GTIN: 87 10895 93414 5
- Quantity: 24
- Gross weight: 5.100 kg

- Tare weight: 1.260 kg
- Net weight: 3.840 kg
- Length (cm): 45.00 cm
- Width (cm): 25.00 cm
- Height (cm): 32.00 cm

## Inner Box

- Gross weight: 0.85 kg
- Inner carton (L x W x H): 23.2 x 14.2 x 14.2 cm
- Net weight: .64 kg
- Tare weight: 0.21 kg

## Outer Box

- Gross weight: 6.16 kg
- Outer carton (L x W x H): 43.6 x 42.4 x 27.7 cm
- Net weight: 2.64 kg
- Tare weight: 3.52 kg

## Packaging dimensions

- Packaging dimensions (W x H x D):  
14 x 22.8 x 3 cm
- Gross weight: .16 kg
- Net weight: 0.11 kg
- Tare weight: .05 kg

SWV3534/10

# Highlights

## Deep Color™

Supports 30-bit, 36-bit and 48-bit (RGB or YCbCr) colour depths, allowing HDTVs to go from millions of colours to billions of colours. Enables increased contrast ratio. Eliminates on-screen colour banding for smooth tonal transitions and subtle gradations between colours.

## Lossless Audio™

Supports new lossless compressed digital audio formats Dolby TrueHD and DTS-HD.

## 24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

## High-purity copper

This copper conductor provides high accuracy in signal transfer with minimal resistance.

## Braided shielding

Copper-braided reinforced aluminium shielding protects against signal loss and interference.

## Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

## Plug and play

Plug and play offers easy installation of components without time-consuming installations.



Issue date 2009-05-31

Version: 7.0.10

12 NC: 9082 100 06296  
EAN: 87 10895 93413 8

© 2009 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)