

Philips  
DVI cable

1,5 m

SWV5565



## Create a superior viewing experience

with this video cable

Experience a new level of viewing while transferring video signals between your components. Superior construction delivers improved picture performance.

### Enjoy superior picture quality

- 24 carat gold-plated connectors optimize signal
- Stranded conductor extends durability
- High-bandwidth Digital Content Protection

### Protects against signal loss

- 100% aluminum shielding
- Oxygen-free copper conductor for ideal signal transfer
- Copper braided reinforced aluminum shielding

### Easy installation

- Non-slip ergonomic grip for easy use
- Plug and play for easy use

### Enjoy extended durability

- Protective metal shell for extended durability
- Super pliable jackets for outstanding flexibility
- Rubber strain relief

# PHILIPS

DVI cable  
1,5 m

# Specifications

## Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 93455 8
- Gross weight: .74 kg
- Tare weight: .13 kg
- Net weight: .61 kg
- Length: 265 mm
- Width: 195 mm
- Height: 100 mm

## Inner Carton

- EAN/UPC/GTIN: 87 10895 97054 9
- Quantity: 2
- Gross weight: 1.82 kg
- Tare weight: .6 kg

- Net weight: 1.22 kg
- Length: 280 mm
- Width: 175 mm
- Height: 210 mm

## Outer Carton

- EAN/UPC/GTIN: 87 10895 97055 6
- Quantity: 4
- Gross weight: 4.31 kg
- Tare weight: 1.87 kg
- Net weight: 2.44 kg
- Length: 370 mm
- Width: 300 mm
- Height: 230 mm

SWV5565/10

# Highlights

## 24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

## Stranded conductor

The stranded wire evenly distributes stress so no single area is overburdened. It provides more flexibility for easier positioning.

## HDCP Compliant

High-bandwidth Digital Content Protection (HDCP) allows you to play protected content media such as movies and concerts. It checks the signal to prevent piracy, allowing only legal copies of content to display.

## 100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

## Twisted high purity OFC

This oxygen-free copper conductor provides the highest accuracy in signal transfer with minimal resistance.

## Braided shielding

Copper braided reinforced aluminum shielding protects against signal loss and interference.

## Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

## Plug and play

Plug and play offers easy installation of components without time-consuming installations.

## Metal shell

The metal shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

## Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.

## Rubber strain relief

Rubber strain relief provides a secure, yet flexible juncture between the cable and the plug.



Issue date 2019-04-24

Version: 2.0.5

12 NC: 9082 100 06365  
EAN: 87 10895 93462 6

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)