



Philips
HDMI cable

4K 60Hz
18 Gbps
1.5 m (4.9 ft)

SWV5613G



HDMI Premium Certified Cable

4K 60Hz Ultra HD with Ethernet

HDMI Premium Certified Cable provides ultra HD 4K resolution at 60 fps. High-speed HDMI supports full 32 channel audio system with up to 1536 KHz sample rate.

Designed for the best picture and sound quality

- 30 AWG pure copper wire for best picture and sound quality.
- Gold-plated connectors for reliable connection.

HDMI Features

- UHD 2160p (4K)
- 3D experience
- Audio Return Channel (ARC)
- 18 Gbps ultra-high-speed data transfer
- 60 Hz frames per second
- 4K resolution (3840 x 2160)

PHILIPS

HDMI cable
4K 60Hz 18 Gbps, 1.5 m (4.9 ft)

Specifications

Packaging dimensions

- Packaging dimensions (W x H x D): 10 x 17 x 6 cm
- Net weight: 0.09 kg
- Gross weight: 0.13 kg
- Tare weight: 0.04 kg
- EAN: 48 95229 12311 3
- Number of products included: 1
- Packaging type: Blister
- Type of shelf placement: Hanging
- Packaging dimensions (W x H x D): 3.9 x 6.7 x 2.4 inch
- Gross weight: 0.287 lb
- Net weight: 0.198 lb
- Tare weight: 0.088 lb

Outer Carton

- Gross weight: 4.12 kg
- Number of consumer packages: 24
- GTIN: 1 48 95229 12311 0

- Tare weight: 1.96 kg
- Gross weight: 9.083 lb
- Tare weight: 4.321 lb
- Outer carton (L x W x H): 15.0 x 15.0 x 9.3 inch
- Outer carton (L x W x H): 38 x 38 x 23.5 cm
- Net weight: 2.16 kg
- Net weight: 4.762 lb

Inner Carton

- GTIN: 2 48 95229 12311 7
- Number of consumer packages: 4
- Gross weight: 1.422 lb
- Gross weight: 0.645 kg
- Inner carton (L x W x H): 7.1 x 4.7 x 5.3 inch
- Inner carton (L x W x H): 18 x 12 x 13.5 cm
- Tare weight: 0.628 lb
- Tare weight: 0.285 kg
- Net weight: 0.36 kg
- Net weight: 0.794 lb

SWV5613G/00

Highlights

60 Hz frames per second

Superior viewing and gaming experience with maximum 60 frames-per-second images.

30 AWG pure copper wire

Quality material usage - 30 AWG pure copper wire to ensure the best connection with minimum data lost.

3D experience

Supports all 3D video formats, allowing true 3D home theatre and gaming applications.

Audio Return Channel (ARC)

Allows an HDMI-connected TV with built-in tuner to send digital audio data to a surround audio system, eliminating the need for a separate audio cable.

4K resolution

Supports video resolution up to 4K (3840 x 2160) to provide the ultimate image quality and gaming experience.



Issue date 2022-05-09

Version: 3.2.3

12 NC: 8670 001 77665
EAN: 48 95229 12311 3

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com