

Philips
Component video cable

5 m

SWV6314



Get a great viewing experience

with this premium video cable

Take your components to optimum performance. This top-of-the-line cable offers the best connection for transferring video signals between components.

Enjoy better picture quality

- 24 carat gold-plated connectors optimise signal
- 4-Cut connectors for secure connections
- Split centre pin for better signal transfer
- 99.97% Oxygen-Free Copper (OFC)

Protects against signal loss

- 100% aluminium shielding
- Copper-braided shielding

Easy installation

- Colour-coded connectors for instant recognition
- Non-slip ergonomic grip for easy use
- Plug and play for easy use

Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility

PHILIPS
sense and simplicity

Component video cable
5 m

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 99405 7
- Gross weight: 1.42 kg
- Tare weight: 0.1 kg
- Net weight: 1.32 kg
- Length: 342 mm
- Width: 255 mm
- Height: 120 mm

Inner Box

- EAN/UPC/GTIN: 87 10895 99406 4
- Quantity: 2
- Gross weight: 3.18 kg
- Tare weight: 0.34 kg

- Net weight: 2.84 kg
- Length: 360 mm
- Width: 242 mm
- Height: 268 mm

Outer Box

- EAN/UPC/GTIN: 87 10895 99407 1
- Quantity: 4
- Gross weight: 7.28 kg
- Tare weight: 0.92 kg
- Net weight: 6.36 kg
- Length: 505 mm
- Width: 376 mm
- Height: 300 mm

SWV6314/10

Highlights

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

4-Cut connectors

4-Cut connectors ensure secure connections between your component and your cable.

Split centre pin

The split centre pin allows for better signal transfer and an improved connection to the component inputs.

99.97% OFC solid conductor

99.97% Oxygen-free copper (OFC) cable core provides optimum signal quality.

100% aluminium shielding

This protective layer of aluminium guards against electromagnetic interference for improved signal quality.

Copper-braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

Colour-coded connectors

Colour-coded connections make it easy to install your cable into the correct inputs and outputs

Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.



Issue date 2009-03-09

Version: 2.0.6

12 NC: 9082 100 09769
EAN: 87 10895 99405 7

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com