

Philips
Component video cable

10 m

SWV6315



Enjoy the ultimate viewing experience

Take your components to optimum performance. This top-of-the-line cable offers the best connection for transferring video signals between components.

Enjoy better picture quality

- 24 carat gold-plated connectors optimise signal
- 4-Cut connectors for secure connections
- 99.97% Oxygen-Free Copper (OFC)
- Split centre pin for better signal transfer

Protects against signal loss

- 100% aluminium shielding
- Copper-braided shielding

Easy installation

- Colour-coded connectors for instant recognition
- Non-slip ergonomic grip for easy use
- Plug and play for easy use

Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility

PHILIPS
sense and simplicity

Component video cable
10 m

Specifications

Inner Box

- EAN/UPC/GTIN: 87 12581 31463 7
- Quantity: 2
- Gross weight: 5.28 kg
- Tare weight: .28 kg
- Net weight: 5 kg
- Length (cm): 35 cm
- Width (cm): 24.5 cm
- Height (cm): 27.5 cm

Outer Box

- EAN/UPC/GTIN: 87 12581 31464 4
- Quantity: 4
- Gross weight: 11.52 kg
- Tare weight: 94 kg

- Net weight: 10.58 kg
- Length (cm): 50 cm
- Width (cm): 37 cm
- Height (cm): 29 cm

Packaging

- EAN/UPC/GTIN: 87 12581 31462 0
- Quantity: 1
- Gross weight: 2.5 kg
- Tare weight: .1 kg
- Net weight: 2.4 kg
- Height: 12 cm
- Length: 33 cm
- Width: 25 cm

SWV6315/10

Highlights

Colour-coded connectors

Colour-coded connections make it easy to install your cable into the correct inputs and outputs

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

100% aluminium shielding

This protective layer of aluminium guards against electromagnetic interference for improved signal quality.

Copper-braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

4-Cut connectors

4-Cut connectors ensure secure connections between your component and your cable.

99.97% OFC solid conductor

99.97% Oxygen-free copper (OFC) cable core provides optimum signal quality.

Split centre pin

The split centre pin allows for better signal transfer and an improved connection to the component inputs.

Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.



Issue date 2009-03-09

Version: 2.0.4

12 NC: 8670 000 26832
EAN: 87 12581 31462 0

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com