

Philips
Scart cable

1,5 m

SWV6320



Enjoy the ultimate viewing experience

with this premium a/v cable

Take your components to optimum performance. This top of the line cable offers the best connection for transferring audio/video signals between components.

Enjoy superior picture quality

- 24 carat gold-plated connectors optimize signal
- 4-Cut connectors for secure connections
- Split center pin for better signal transfer
- 99.97% Oxygen-Free Copper (OFC)

Protects against signal loss

- 100% aluminum shielding
- Oxygen-free copper conductor for ideal signal transfer
- Copper braided shielding
- Foam Polyethylene (FPE) Dielectric

Easy installation

- Color coded connectors for instant recognition
- Non-slip ergonomic grip for easy use
- Plug and play for easy use

PHILIPS

Scart cable
1,5 m

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 93472 5
- Gross weight: .55 kg
- Tare weight: .13 kg
- Net weight: .42 kg
- Length: 265 mm
- Width: 195 mm
- Height: 80 mm

Inner Carton

- EAN/UPC/GTIN: 87 10895 97040 2
- Quantity: 2
- Gross weight: 1.44 kg
- Tare weight: .6 kg

- Net weight: .84 kg
- Length: 280 mm
- Width: 175 mm
- Height: 210 mm

Outer Carton

- EAN/UPC/GTIN: 87 10895 97041 9
- Quantity: 4
- Gross weight: 3.55 kg
- Tare weight: 1.87 kg
- Net weight: 1.68 kg
- Length: 370 mm
- Width: 300 mm
- Height: 230 mm

SWV6320/10

Highlights

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

4-Cut connectors

4-Cut connectors ensure secure connections between your component and your cable.

Split center pin

The split center pin allows for better signal transfer and an improved connection to the component inputs.

99.97% OFC solid conductor

99.97% Oxygen-free copper (OFC) cable core provides optimum signal quality.

100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

Twisted high purity OFC

This oxygen-free copper conductor provides the highest accuracy in signal transfer with minimal resistance.

Copper braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

FPE Dielectric

Foam Polyethylene (FPE) dielectric is a superior insulation material that protects against signal loss.

Color-coded connectors

Color coded connections make it easy to install your cable into the correct inputs and outputs

Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.



Issue date 2019-04-24

Version: 2.0.10

12 NC: 9082 100 06391
EAN: 87 10895 93472 5

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com