

Philips  
HDMI/DVI conversion  
cable

1,5 m

SWV6372



## Enjoy the ultimate viewing experience

with this premium video cable

Take your components to optimum performance. This top of the line cable offers the best connection for transferring video signals between components.

### Enjoy superior picture quality

- 24 carat gold-plated connectors optimize signal
- 99.97% Oxygen-Free Copper (OFC)
- High-bandwidth Digital Content Protection

### Protects against signal loss

- 100% aluminum shielding
- Oxygen-free copper conductor for ideal signal transfer
- Copper braided shielding
- Foam Polyethylene (FPE) Dielectric

### Easy installation

- Non-slip ergonomic grip for easy use

### Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility
- Reliable metal strain relief

# PHILIPS

HDMI/DVI conversion cable  
1,5 m

# Specifications

## Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 93479 4
- Gross weight: .35 kg
- Tare weight: .01 kg
- Net weight: .34 kg
- Length: 273 mm
- Width: 197 mm
- Height: 89 mm

## Outer Carton

- EAN/UPC/GTIN: 87 10895 94983 5
- Quantity: 4
- Gross weight: 1.37 kg
- Tare weight: .01 kg
- Net weight: 1.36 kg
- Length: 323 mm
- Width: 300 mm
- Height: 211 mm

SWV6372/10

# Highlights

## 24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

## 99.97% OFC solid conductor

99.97% Oxygen-free copper (OFC) cable core provides optimum signal quality.

## HDCP Compliant

High-bandwidth Digital Content Protection (HDCP) allows you to play protected content media such as movies and concerts. It checks the signal to prevent piracy, allowing only legal copies of content to display.

## 100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

## Solid high purity OFC

This oxygen-free copper conductor provides the highest accuracy in signal transfer with minimal resistance.

## Copper braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

## FPE Dielectric

Foam Polyethylene (FPE) dielectric is a superior insulation material that protects against signal loss.

## Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

## Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

## Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.

## Metal strain relief

Full metal connector ensures extended durability by preventing damage during use and installation.



Issue date 2019-04-24

Version: 2.1.7

12 NC: 9082 100 07369  
EAN: 87 10895 94990 3

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)