


Philips
HDMI cable

5 m

SWV6373



Enjoy the ultimate viewing experience

with this premium a/v cable

Take your components to optimum performance. This top of the line cable offers the best connection for transferring audio and video signals between components.

Enjoy superior picture quality

- 24 carat gold-plated connectors optimize signal
- 99.97% Oxygen-Free Copper (OFC)
- High-bandwidth Digital Content Protection

Protects against signal loss

- 100% aluminum shielding
- Oxygen-free copper conductor for ideal signal transfer
- Copper braided shielding
- Foam Polyethylene (FPE) Dielectric

Easy installation

- Plug and play for easy use

Enjoy extended durability

- Super pliable jackets for outstanding flexibility

PHILIPS

HDMI cable
5 m

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 95435 8
- Gross weight: .53 kg
- Tare weight: .13 kg
- Net weight: .40 kg
- Length: 285 mm
- Width: 200 mm
- Height: 90 mm

Inner Carton

- EAN/UPC/GTIN: 87 10895 97681 7
- Quantity: 2
- Gross weight: 1.4 kg
- Tare weight: .6 kg

- Net weight: .8 kg
- Length: 315 mm
- Width: 150 mm
- Height: 210 mm

Outer Carton

- EAN/UPC/GTIN: 87 10895 97682 4
- Quantity: 4
- Gross weight: 3.44 kg
- Tare weight: 1.84 kg
- Net weight: 1.6 kg
- Length: 330 mm
- Width: 325 mm
- Height: 235 mm

SWV6373/93

Highlights

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

Copper braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

99.97% OFC solid conductor

99.97% Oxygen-free copper (OFC) cable core provides optimum signal quality.

HDCP Compliant

High-bandwidth Digital Content Protection (HDCP) allows you to play protected content media such as movies and concerts. It checks the signal to prevent piracy, allowing only legal copies of content to display.

FPE Dielectric

Foam Polyethylene (FPE) dielectric is a superior insulation material that protects against signal loss.

Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.



Issue date 2014-02-05

Version: 5.0.8

12 NC: 9082 100 07607
EAN: 87 10895 95435 8

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com