

Philips
HDMI/DVI conversion
cable

3.0 m

SWV6375



Enjoy the ultimate viewing experience

with this premium video cable

Take your components to optimum performance. This premium video cable offers the best connection for transferring video signals between components.

Enjoy superior picture quality

- 24 carat gold-plated connectors optimize signal
- 99.97% Oxygen-Free Copper (OFC)
- High-bandwidth Digital Content Protection

Protects against signal loss

- Copper braided shielding
- 100% aluminum shielding
- Oxygen-free copper conductor for ideal signal transfer

Easy installation

- Non-slip ergonomic grip for easy use
- Plug and play for easy use

Enjoy extended durability

- Heavy-duty brass shell for extended durability

PHILIPS

HDMI/DVI conversion cable
3.0 m

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 94902 6
- Gross weight: .46 kg
- Tare weight: .01 kg
- Net weight: .45 kg
- Length: 273 mm
- Width: 197 mm
- Height: 89 mm

Inner Carton

- EAN/UPC/GTIN: 87 10895 95397 9
- Quantity: 2
- Gross weight: .92 kg
- Tare weight: .01 kg

- Net weight: .91 kg
- Length: 282 mm
- Width: 197 mm
- Height: 175 mm

Outer Carton

- EAN/UPC/GTIN: 87 10895 95398 6
- Quantity: 4
- Gross weight: 1.83 kg
- Tare weight: .01 kg
- Net weight: 1.82 kg
- Length: 323 mm
- Width: 300 mm
- Height: 211 mm



SWV6375/10

Highlights

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

99.97% OFC solid conductor

99.97% Oxygen-free copper (OFC) cable core provides optimum signal quality.

HDCP Compliant

High-bandwidth Digital Content Protection (HDCP) allows you to play protected content media such as movies and concerts. It checks the signal to prevent piracy, allowing only legal copies of content to display.

Copper braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.



Issue date 2019-04-24

Version: 3.2.8

12 NC: 9082 100 07327
EAN: 87 10895 94902 6

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com