

Philips  
HDMI/DVI conversion  
cable

3.0 m

SWV6375



## Enjoy the ultimate viewing experience

with this premium video cable

Take your components to optimum performance. This top of the line cable offers the best connection for transferring video signals between components.

### Enjoy superior picture quality

- 24 carat gold-plated connectors optimize signal
- 99.97% Oxygen-Free Copper (OFC)
- High-bandwidth Digital Content Protection

### Protects against signal loss

- Copper braided shielding
- Foam Polyethylene (FPE) Dielectric
- 100% aluminum shielding

### Easy installation

- Non-slip ergonomic grip for easy use
- Plug and play for easy use

### Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility
- Reliable metal strain relief

# PHILIPS

HDMI/DVI conversion cable  
3.0 m

# Specifications

## Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 95426 6
- Gross weight: .42 kg
- Tare weight: .13 kg
- Net weight: .29 kg
- Length: 285 mm
- Width: 200 mm
- Height: 90 mm

## Inner Carton

- EAN/UPC/GTIN: 87 10895 97685 5
- Quantity: 2
- Gross weight: 1.18 kg
- Tare weight: .6 kg

- Net weight: .58 kg
- Length: 315 mm
- Width: 150 mm
- Height: 210 mm

## Outer Carton

- EAN/UPC/GTIN: 87 10895 97686 2
- Quantity: 4
- Gross weight: 3 kg
- Tare weight: 1.84 kg
- Net weight: 1.16 kg
- Length: 330 mm
- Width: 325 mm
- Height: 235 mm

SWV6375/93

# Highlights

## 24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

## 99.97% OFC solid conductor

99.97% Oxygen-free copper (OFC) cable core provides optimum signal quality.

## HDCP Compliant

High-bandwidth Digital Content Protection (HDCP) allows you to play protected content media such as movies and concerts. It checks the signal to prevent piracy, allowing only legal copies of content to display.

## Copper braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

## FPE Dielectric

Foam Polyethylene (FPE) dielectric is a superior insulation material that protects against signal loss.

## 100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

## Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

## Plug and play

Plug and play offers easy installation of components without time-consuming installations.

## Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

## Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.

## Metal strain relief

Full metal connector ensures extended durability by preventing damage during use and installation.



Issue date 2014-02-07

Version: 4.0.8

12 NC: 9082 100 07585  
EAN: 87 10895 95426 6

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)