

Philips
HDMI/DVI conversion
cable

5 m

SWV6376



Enjoy the ultimate viewing experience

with this premium video cable

Take your components to optimum performance. This top of the line cable offers the best connection for transferring video signals between components.

Enjoy superior picture quality

- 24 carat gold-plated connectors optimize signal
- 99.97% Oxygen-Free Copper (OFC)
- High-bandwidth Digital Content Protection

Protects against signal loss

- 100% aluminum shielding
- Oxygen-free copper conductor for ideal signal transfer
- Copper braided shielding
- Foam Polyethylene (FPE) Dielectric

Easy installation

- Plug and play for easy use

Enjoy extended durability

- Heavy-duty brass shell for extended durability
- Super pliable jackets for outstanding flexibility
- Reliable metal strain relief

PHILIPS

Specifications

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 87 10895 95434 1
- Gross weight: .58 kg
- Tare weight: .13 kg
- Net weight: .45 kg
- Length: 285 mm
- Width: 200 mm
- Height: 90 mm

Inner Carton

- EAN/UPC/GTIN: 87 10895 97687 9
- Quantity: 2
- Gross weight: 1.5 kg
- Tare weight: .6 kg

- Net weight: .9 kg
- Length: 315 mm
- Width: 150 mm
- Height: 210 mm

Outer Carton

- EAN/UPC/GTIN: 87 10895 97688 6
- Quantity: 4
- Gross weight: 3.64 kg
- Tare weight: 1.84 kg
- Net weight: 1.80 kg
- Length: 330 mm
- Width: 325 mm
- Height: 235 mm

Highlights

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

100% aluminum shielding

This protective layer of aluminum guards against electromagnetic interference for improved signal quality.

Copper braided shielding

This protective layer of copper blocks radio frequency interference for improved signal quality.

99.97% OFC solid conductor

99.97% Oxygen-free copper (OFC) cable core provides optimum signal quality.

HDCP Compliant

High-bandwidth Digital Content Protection (HDCP) allows you to play protected content media such as movies and concerts. It checks the signal to prevent piracy, allowing only legal copies of content to display.

FPE Dielectric

Foam Polyethylene (FPE) dielectric is a superior insulation material that protects against signal loss.

Heavy-duty brass shell

The heavy-duty brass shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

Super pliable jackets

Super pliable PVC jackets are abrasion-resistant for outstanding flexibility and protection against everyday wear and tear.

Metal strain relief

Full metal connector ensures extended durability by preventing damage during use and installation.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

