

Philips  
Wireless Headphone

40mm drivers/closed-back  
Bluetooth®

TAH5255BK



## Here comes the amazing sound

On your ears and feel that plentiful layers of sound! These wireless headphones provide you AAC audio code, more clear and more amazing. Classic metal painting brings you exquisite life. You get up to 29 hours play time.

### **29 hours play time. Big bold bass.**

- 40mm drivers feature an optimized vibration system
- Great sound isolation from the closed-back design

### **Easy connection. Easy control.**

- Detachable inline cable. Go wired and keep listening.
- Multi-function button. Easily control music and calls
- Rock-solid Bluetooth connectivity. Easy control.
- Multipoint connection provides your super convenience

### **Matte style. Maximum comfort.**

- Eye-catching matte colorways

### **Maximum comfort. Maximum style.**

- Lightweight, adjustable cushioned headband.
- Soft ear cups that can be angled for maximum comfort

# PHILIPS

Wireless Headphone  
40mm drivers/closed-back Bluetooth®

# Specifications

## Accessories

- Quick Start Guide

## Connectivity

- Bluetooth profiles: A2DP, AVRCP, HFP, HSP
- Bluetooth version: 5.0
- Maximum range: Up to 10 m
- Microphone: Built-in microphone

## Convenience

- Call Management: Answer/End Call, Call on Hold, Reject Call, Switch between 2 calls, Switch between call and music
- Volume control

## Design

- Color: Black

## Power

- Battery type: Li-Polymer
- Music play time: 30 hr
- Standby time: 630
- Talk time: 29 hr

## Sound

- Magnet type: NdFeB

- Type: dynamic
- Acoustic system: Closed
- Frequency response: 20 - 20 000 Hz
- Impedance: 32 ohm
- Sensitivity: 110 dB
- Speaker diameter: 32 mm

## Outer Carton

- Gross weight: 2.043 kg
- GTIN: 1 48 95229 11716 4
- Outer carton (L x W x H): 42 x 19 x 25 cm
- Nett weight: 0.85 kg
- Number of consumer packagings: 5
- Tare weight: 1.193 kg

## Packaging dimensions

- Packaging dimensions (W x H x D): 14.7 x 17.5 x 7.5 cm
- EAN: 48 95229 11716 7
- Gross weight: 0.319 kg
- Nett weight: 0.17 kg
- Number of products included: 1
- Packaging type: Carton
- Tare weight: 0.149 kg
- Type of shelf placement: Both

TAH5255BK/97

# Highlights

## Detachable inline cable

Detachable inline cable. Go wired and keep listening.

## Multi-function button.

Don't like the current track? Skip it with a long press. Want to reject a call? A simple button-press takes care of that. Smart Bluetooth pairing means these earphones remember the last devices they were paired with.

## Rock-solid connectivity

Rock-solid Bluetooth connectivity. Easy control.

## Eye-catching matte colorways

Eye-catching matte colorways

## Lightweight cushioned headband

Available in stylish matte colorways, these on-ear headphones boast a cushioned headband that's so light you'll barely feel it. The soft ear cups are clearly marked for left/right ears, and can be angled until they feel just right.


## Soft ear cups

Soft ear cups that can be angled for maximum comfort

## 40 mm neodymium drivers H5255

These headphones boast powerful 40 mm neodymium acoustic drivers that give you crisp sound and rich bass

## Great sound isolation from the



Great sound isolation from the closed-back design

## Multipoint Connection H5255

Your headphone can connect more than one Bluetooth equipments, mobile phones, tablet computers and laptops, feel free to convert your devices at your super convenience



Issue date 2022-05-29

Version: 3.0.1

12 NC: 8670 001 73581  
EAN: 48 95229 11716 7

© 2022 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)