

Philips  
Wireless Headphone

40mm drivers/closed-back  
Bluetooth®

TAH5255WT



## Here comes the amazing sound

On your ears and feel that plentiful layers of sound! These wireless headphones provide you AAC audio code, more clear and more amazing. Classic metal painting brings you exquisite life. You get up to 29 hours play time.

### **29 hours play time. Big bold bass.**

- 40mm drivers feature an optimized vibration system
- Great sound isolation from the closed-back design

### **Easy connection. Easy control.**

- Multi-function button. Easily control music and calls
- Rock-solid Bluetooth connectivity. Easy control.
- Detachable inline cable. Go wired and keep listening.
- Multipoint connection provides your super convenience

### **Maximum comfort. Maximum style.**

- Lightweight, adjustable cushioned headband.
- Soft ear cups that can be angled for maximum comfort

# PHILIPS

Wireless Headphone  
40mm drivers/closed-back Bluetooth®

# Specifications

## Sound

- Acoustic system: Closed
- Magnet type: NdFeB
- Frequency response: 20 - 20 000 Hz
- Impedance: 32 ohm
- Speaker diameter: 32 mm
- Sensitivity: 110 dB
- Type: dynamic

## Connectivity

- Microphone: Built-in microphone
- Bluetooth profiles: A2DP, AVRCP, HFP, HSP
- Bluetooth version: 5.0
- Maximum range: Up to 10 m

## Convenience

- Volume control
- Call Management: Call on Hold, Switch between 2 calls, Answer/End Call, Reject Call, Switch between call and music

## Accessories

- Quick Start Guide

## Power

- Battery type: Li-Polymer

- Standby time: 630
- Talk time: 29 hr
- Music play time: 30 hr

## Design

- Color: Black

## Packaging dimensions

- Packaging type: Carton
- Number of products included: 1
- Type of shelf placement: Both
- Packaging dimensions (W x H x D): 14.7 x 17.5 x 7.5 cm
- Gross weight: 0.319 kg
- Nett weight: 0.17 kg
- Tare weight: 0.149 kg
- EAN: 48 95229 11717 4

## Outer Carton

- Number of consumer packagings: 5
- Outer carton (L x W x H): 42 x 19 x 25 cm
- Gross weight: 2.043 kg
- Nett weight: 0.85 kg
- Tare weight: 1.193 kg
- GTIN: 1 48 95229 11717 1

TAH5255WT/97

# Highlights

## Detachable inline cable

Detachable inline cable. Go wired and keep listening.

## Lightweight cushioned headband

Available in stylish matte colorways, these on-ear headphones boast a cushioned headband that's so light you'll barely feel it. The soft ear cups are clearly marked for left/right ears, and can be angled until they feel just right.

## Multi-function button.

Don't like the current track? Skip it with a long press. Want to reject a call? A simple button-press takes care of that. Smart Bluetooth pairing means these earphones remember the last devices they were paired with.

## Rock-solid connectivity

Rock-solid Bluetooth connectivity. Easy control.


## Soft ear cups

Soft ear cups that can be angled for maximum comfort

## 40 mm neodymium drivers H5255

These headphones boast powerful 40 mm neodymium acoustic drivers that give you crisp sound and rich bass

## Great sound isolation from the



Great sound isolation from the closed-back design

## Multipoint Connection H5255

Your headphone can connect more than one Bluetooth equipments, mobile phones, tablet computers and laptops, feel free to convert your devices at your super convenience



Issue date 2022-05-30

Version: 3.0.1

12 NC: 8670 001 73582  
EAN: 48 95229 11717 4

© 2022 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)