



Philips
Portable Radio

FM/AM

Analog tuning
AC or battery power



TAR2506

The classic companion

From kitchen to bathroom to garage, add a dash of traditional style to your listening. This classic FM/AM analog radio is easy to tune, sounds great, and it looks great too. Heading outside? This radio runs off AC or battery power.

Traditional style

- Classic design. Easy to tune
- Analog FM/AM radio
- Large traditional-style tuning window

The radio you love

- Simple controls. Large volume dial
- Good clear sound. 3.5" speaker
- Headphone port for private listening
- Switch between News and Music modes. Tone control

Flexible placement

- Place it anywhere
- AC or battery operated (2x D batteries)
- Dimensions: 210x149x66.3 mm

PHILIPS

Portable Radio
FM/AM Analog tuning, AC or battery power

Specifications

Tuner/Reception/Transmission

- Tuner bands: FM, AM
- RDS: No

Sound

- Output power (RMS): 300 mW
- Sound System: Mono
- Sound enhancement: tone control
- Volume control: rotary (analogue)

Loudspeakers

- Number of full range drivers: 1
- Full range driver diameter: 3.5"

Connectivity

- Audio/Video output: Headphone (3.5mm)
- Audio in: No
- Bluetooth: No

Alarm

- No. of alarms: No
- Snooze (repeat alarm): No

Power

- Power supply: 110-120V, 50/60 Hz
- Battery type: D size (LR20)
- Battery voltage: 1.5 V
- Number of batteries: 2

Accessories

- Included accessories: AC Power Cord, Quick start guide, Warranty certificate

Product dimensions

- Product dimensions (W x H x D): 21 x 14.9 x 6.63 cm
- Product dimensions (W x H x D): 8.3 x 5.9 x 2.6 inch
- Weight: 1.543 lb
- Weight: 0.7 kg

Packaging dimensions

- UPC: 8 40063 20266 5
- Packaging dimensions (W x H x D): 23.5 x 19.5 x 9 cm
- Packaging dimensions (W x H x D): 9.3 x 7.7 x 3.5 inch
- Gross weight: 1.007 kg
- Gross weight: 2.220 lb
- Nett weight: 0.837 kg
- Nett weight: 1.845 lb
- Tare weight: 0.17 kg
- Tare weight: 0.375 lb
- Number of products included: 1
- Packaging type: Box
- Type of shelf placement: Laying

TAR2506/37

Highlights

Classic design. Easy to tune

This analog FM/AM radio looks great in almost any room. A large traditional-style tuning window makes it easy to see when you have reached the desired frequency. Simply turn the side-mounted tuning wheel to slide the indicator along the scale.

Tone control



Make the most of your music with Music mode. Switch to News mode when you're listening to the news, or your favorite radio soap or panel show. Whatever you love, a 3.5" speaker ensures good clear sound.

Simple controls

You'll never need to search for the volume control on this radio! In addition to the large volume dial, the radio boasts top-mounted switches for switching between FM/AM signals and sound modes. You'll also find a headphone port for private listening.

Place it anywhere

Wherever you love to listen, this radio can come with you. Plug the radio into a wall outlet, or insert two D batteries and go outside. It's the perfect companion for a glass of wine on the balcony, or a picnic in the backyard.



Issue date 2022-07-22

Version: 1.0.1

12 NC: 8670 001 85604
UPC: 8 40063 20266 5

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com